





GE
Lighting


80893 - FLE16/2/R30XL827

GE Floodlight Soft White R30 - Facilities; Retail Display; Hospitality; Office; Restaurant

a product of
ecomagination



 High Color Rendering
cUL Listed
Energy Savings
 UL Listed



GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	R30
Base	Medium Screw (E26)
Equivalent Wattage	65.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
LEED-EB MR Credit	467 picograms Hg per mean lumen hour
Primary Application	Indoor Floodlight;Facilities;Retail Display;Hospitality;Office;Restaurant

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	750.0
Mean Lumens	600.0
Nominal Initial Lumens per Watt	50
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

ELECTRICAL CHARACTERISTICS

Wattage	16.0
Input Voltage	120.0 V
Input Current	0.2300 A

DIMENSIONS

Maximum Overall Length (MOL)	5.5000 in(139.7 mm)
Nominal Length	5.500 in(139.7 mm)

PRODUCT INFORMATION

Product Code	80893
Description	FLE16/2/R30XL827
Standard Package	Case
Standard Package GTIN	10043168808931
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168808934

CAUTIONS & WARNINGS

Warning

- Risk of Electric Shock
 - Do not open - no user serviceable parts inside.
 - Do not use where directly exposed to water or outdoors without an enclosed fixture.



GE
Lighting


80893 - FLE16/2/R30XL827

GE Floodlight Soft White R30 - Facilities; Retail Display; Hospitality; Office; Restaurant

a product of
ecomagination



High Color Rendering
cUL Listed
Energy Savings
UL Listed



GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	R30
Base	Medium Screw (E26)
Equivalent Wattage	65.0 W
Rated Life	10000.0 hrs
Starting Temperature (MIN)	-15.0 °C
LEED-EB MR Credit	467 picograms Hg per mean lumen hour
Primary Application	Indoor Floodlight;Facilities;Retail Display;Hospitality;Office;Restaurant

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	750.0
Mean Lumens	600.0
Nominal Initial Lumens per Watt	50
Color Temperature	2700.0 K
Color Rendering Index (CRI)	82.0

ELECTRICAL CHARACTERISTICS

Wattage	16.0
Input Voltage	120.0 V
Input Current	0.2300 A

DIMENSIONS

Maximum Overall Length (MOL)	5.5000 in(139.7 mm)
Nominal Length	5.500 in(139.7 mm)

PRODUCT INFORMATION

Product Code	80893
Description	FLE16/2/R30XL827
Standard Package	Case
Standard Package GTIN	10043168808931
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168808934

CAUTIONS & WARNINGS

Warning

- Risk of Electric Shock
 - Do not open - no user serviceable parts inside.
 - Do not use where directly exposed to water or outdoors without an enclosed fixture.