

Ground Fault Products Heavy Duty Commercial & Hospital Grade GFCI Receptacles Tamper-Resistant and Weather Resistant with Auto Grounding

UL  SP 
Meets UL Standard 943
Class A GFCI




GFTR201

10kA Short Circuit Current Rating

- Limits improper access to energized contacts
 - Patented shutter design for tamper-resistant protection
- No power at face if reverse wired
 - Open circuit condition eliminates false assumption of protection at face
- Ground fault EOL indicator
 - Flashing **RED** indicates device has lost capability to provide protection
- Accepts fork terminals
 - Open terminal design
- Installation ease
 - Internal back wiring
 - Automatic self-grounding staple
 - Captive mounting screws

Circuit Guard® GFCI Receptacles Tamper-Resistant and Weather Resistant

Description	Rating	Color	Catalog Number	
Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFTR15BK	GFTR20BK
		Brown	GFTR15	GFTR20
		Gray	GFTR15GY	GFTR20GY
		Ivory	GFTR15I	GFTR20I
		Light Almond	GFTR15LA	GFTR20LA
		Red	GFTR15R	GFTR20R
		White	GFTR15W	GFTR20W



GFTR15AL

Circuit Guard® GFCI Receptacles - 3 Pack Tamper-Resistant and Weather Resistant

Description	Rating	Color	Catalog Number	
3 Pack, flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Ivory	GFTR15I3	GFTR20I3
		Light Almond	GFTR15LA3	GFTR20LA3
		White	GFTR15W3	GFTR20W3

Note: Consult factory for availability of other colors.

Circuit Guard® GFCI Receptacles Tamper-Resistant and Weather Resistant

Description	Rating	Color	Catalog Number	
Hospital Grade ● Flush, nylon face, back and side wired, multiple drive screws, self-grounding staple.	15 and 20A 125V AC	Black	GFR8200HBKTR	GFR8300HBKTR
		Brown	GFR8200HTR	GFR8300HTR
		Gray	GFR8200HGYTR	GFR8300HGYTR
		Ivory	GFR8200HITR	GFR8300HITR
		Light Almond	GFR8200HLATR	GFR8300HLATR
		Red	GFR8200HRTR	GFR8300HRTR
		White	GFR8200HWTR	GFR8300HWTR



GFR8300HRTR

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with a matching color nylon wallplate. 20 amp feed-through capability. See page Tech-10 for Tamper-Resistant and Weather Resistant descriptions.

Safety and Economy



GF15ILA

10kA Short Circuit Current Rating

- Comprehensive diagnostics
 - When test button is actuated, both the electronic components and mechanical trip mechanism are functionally tested
- Ground fault indicator
 - Flashing **RED** indicates device has lost capability to provide protection
- No power at face if reverse wired
 - Open circuit condition eliminates false assumption of protection at face
- Installation ease
 - Internal back wiring
 - Automatic grounding feature
 - Captive mounting screws



GF15ILA







GFTR20I



GFBF20ILA

GFCI Duplex Receptacles, Flush Nylon Face, Matching Nylon Wallplate Included

Description	 Weather and Tamper-Resistant	 15A 125V NEMA 5-15R UL/CSA Standard	 Weather and Tamper-Resistant	 20A 125V NEMA 5-20R UL/CSA Standard
	Termination	Self-Grounding, Back and Side Wire	Self-Grounding, Back and Side Wire	Self-Grounding, Back and Side Wire
Rating	15A 125V AC NEMA 5-15R	15A 125V AC NEMA 5-15R	20A 125V AC NEMA 5-20R	20A 125V AC NEMA 5-20R
Black	GFTR15BK	GF15BKLA	GFTR20BK	GF20BKLA
Brown	GFTR15	GF15LA	GFTR20	GF20LA
Gray	GFTR15GY	GF15GYLA	GFTR20GY	GF20GYLA
Ivory	GFTR15I	GF15ILA	GFTR20I	GF20ILA
Light Almond	GFTR15LA	GF15LALA	GFTR20LA	GF20LALA
Red	GFTR15R	GF15RLA	GFTR20R	GF20RLA
White	GFTR15W	GF15WLA	GFTR20W	GF20WLA

Note: See page Tech-10 for Weather and Tamper-Resistant descriptions.
 Bulk 50 pack available without plates, add **"BULK"** suffix. Example: **GFTR20WBULK**.

GFCI Faceless Receptacles, Flush Nylon Face, Matching Nylon Wallplate Included

Description	Circuit Guard® Faceless
Termination	Self-Grounding, Back and Side Wire
Rating	20A 125V NEMA 5-20R
Black	GFBF20BKLA
Brown	GFBF20LA
Gray	GFBF20GYLA
Ivory	GFBF20ILA
Light Almond	GFBF20LALA
Red	GFBF20RLA
White	GFBF20WLA