



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GP6426 Ground Rod to Cable

Burndy LLC

Catalog Number	GP6426
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 2 Cables to Rod or Pipe, 4 Awg (Sol.) - 2/0 Awg (STR.), 3/8" Pipe, 5/8" - 3/4" Rod, 3/8" Stud.
Weight per unit	0.5500 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Bolt Size	3/8 in
Material	COPPER ALLOY

### Descriptions

Description	GROUND ROD TO CABLE
extra long description	BUR GP6426 4SOL-2/0STR, 3/8 IPS, 2
Long Description	Mechanical Grounding Connector, 2 Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 3/8" Pipe, 5/8" - 3/4" Rod, 3/8" Stud.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Parallel Cables Perpendicular To Rod, Pipe Or Column, Also Used With One Groove For Run, The Other For Tap To Equipment, High Copper Alloy Cast Body And DURIMUM U-Bolts, Nuts, And Lockwashers Make The GP Suitable For Direct Burial In The Ground Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Ground Rod Size: 5/8 - 3/4 IN, Tube (ips) Size: 3/8 IN, Width: 2-1/8 IN, Installation Torque: 24

### Manufacturer Information

Brand	BURNDY
GTIN	00781810260548
Manufacturers Part Number	GP6426
UPC	781810260548

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GP

### Packaging

Carton	1
Weight Per each	0.55



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application

For Joining A Range Of Parallel Copper Cables Perpendicular To  
Rod, Pipe Or Column, Direct Burial In Earth Or Concrete

standard

UL467