



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHB2045 Type GHB BRKR 2P 45A 277/480VAC Max 125/250VDC Max Eaton Corp

Catalog Number	GHB2045
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 45 A, 480Y/277 Vac, 125/250 VDC, 65 Kaic At 240 Vac, 14 Kaic At 480Y/277 Vac, 50/60 HZ
Weight per unit	1.1 (lbs/each)
Product Category	2 Pole

Features

Current Rating	45 A
dimensions	2.6300 IN X 2.0000 IN X 4.0000 IN
frame	G
media	Yes
Poles	2
Voltage Rating	480Y/277 Vac, 125/250 Vdc

Descriptions

Description	TYPE GHB BRKR 2P 45A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHB2045 GHB CB 2P 45A 277/480VA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 45 A, 480Y/277 Vac, 125/250 Vdc, 65 kAIC at 240 Vac, 14 kAIC at 480Y/277 Vac, 50/60 Hz
Product Type	GHB CB 2P 45A 277/480VAC Max 125/250VDC

Manufacturer Information

Brand	Eaton
GTIN	00786679911457
Manufacturers Part Number	GHB2045
UPC	786679911457

Taxonomies, Classifications, and Categories

Type	Molded case circuit breaker
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.1

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed, Federal Specifications Classification W-C375B