

## DESCRIPTION

The HBI series is an outstanding solution for high mounting height industrial or retail applications. The HBI optic has been optimized to provide maximum performance from T8 lamps. Optional uplight component is provided to enable excellent ceiling uniformity. HBI's high lumen package allows the benefits of fluorescent to be applied at high mounting heights that were traditionally exclusive to H.I.D. The primary benefits include exceptional color rendering, high system efficacy, 95% lumen maintenance, long lamp life, instant on/instant re-strike, economical dimming, and uniform brightness control. Primary applications include retail, shopping malls, light industrial, gymnasiums and recreational environments.

## SPECIFICATION FEATURES

### Construction

Full bodied steel housing with integral ballast channel adds strength, rigidity and structural protection for optical assembly.

### Electrical

The HBI comes with a standard Class P electronic ballast and twistlock lampholders. UL/cUL listed for high ambient environments up to 55°C (131°F) for all lamps and ballast combinations when used in open upright configurations. Suitable for damp locations. Optional modular power receptacle meets UL2459 and NEC 410.73 and is UL/cUL rated for make and break under load from outside the luminaire to speed maintenance.

### Finish

White enamel finish preceded by a multistage cleaning cycle, iron phosphate coating with rust inhibitor to protect against contaminants and oxidation.

### Downlight/Uplight Optics

Die formed, segmented optical design optimizes performance across three distributions. Optical choices include a narrow distribution for aisles, medium distribution for assembly and loading areas, or wide distribution for general, open area lighting. An uplight option is offered to permit ceiling uniformity and allow for ample lamp and luminaire heat dissipation. Gasketed door frame & lens assembly is optional for more demanding environments.

Catalog #		Type
Project		
Comments		Date
Prepared by		

### Options

Integral Occupancy Sensor available and provides from 600 sq. ft. (MS) up to 1250 sq. ft. (MSO) of coverage in a maximum mounting height of 40' using interchangeable lens caps provided.

### Mounting

The HBI series is suited for suspension mounting with optional wire hook and chain set or cable mounting. Single monopoint mounting is available with SPM Tong Hanger.

### Warranty

When operated in high ambient conditions, the HBI is supported by a 5 yr/55°C and 3 yr/65°C ballast warranty when used with a high power factor ballast in open, upright configurations. To maximize your warranty, the HBI should be ordered with a high power factor ballast in ambient environments that typically exceed 40°C (102°F).



## HBI SERIES

6 T8 LAMPS

High-Bay Industrial  
Fluorescent Luminaire



## ENERGY DATA

Input Watts:

**EB Ballast**  
632=169W

**EB/Plus Ballast**  
632=218W

**ER Ballast**  
632=169W

**ER/Plus Ballast**  
632=218W

Luminaire Efficacy Rating

**LER = FL-84** (Narrow Beam)

**Catalog Number:** HBI-632-N-UPL

**Yearly Cost of 1000 lumens,**  
3000 hrs at .08 KWH = \$2.85

\*Reference the lamp/ballast data in the  
Technical Section for specific lamp/ballast  
requirements.

\*\*Consult Pre Sales Technical Support.


**LAMPS CONTAIN MERCURY. DISPOSE ACCORDING  
TO LOCAL, STATE OR FEDERAL LAWS**

**LINEAR DISCONNECT**


Safe and convenient means of  
disconnecting power.

ADF091043


2016-07-12 14:50:46



## LAMP CONFIGURATIONS




## DIMENSION TOP VIEW



Powering Business Worldwide

PHOTOMETRICS



**HBI-632-N-UNV-EB82**  
 Electronic Ballasts  
 (6) 32WT8 Lamps  
 2850 lumens  
 Spacing criterion:  
 (H) 1.3 x mounting  
 height, (L) 1.1 x  
 mounting height  
 Efficiency 91.3%  
 Test Report:  
 HBI632.IES  
 LER =FL81  
 Yearly Cost of 1000  
 lumens, 3000 hrs at  
 .08 KWH = \$2.95

Candela				
Angle	Along H	45°	Across L	
0	5981	5981	5981	
5	6000	5958	5900	
10	5959	5716	5516	
15	5861	5330	4953	
20	5702	4832	4572	
25	5468	4418	4452	
30	5189	4191	4398	
35	4862	3996	4222	
40	4491	3834	3894	
45	4085	3563	3314	
50	3649	3169	2953	
55	3186	2598	2657	
60	2699	2220	2469	
65	2193	1914	2291	
70	1668	1693	1766	
75	1144	1291	1226	
80	635	760	703	
85	194	274	227	
90	10	14	14	

Coefficients of Utilization

rc rw RCR	Effective floor cavity reflectance 20%																	
	80%				70%				50%				10%					
	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
0	109	109	109	109	106	106	106	106	101	101	101	97	97	97	93	93	93	91
1	99	94	90	87	96	92	89	85	89	85	83	85	82	80	82	80	78	76
2	90	82	76	70	87	80	74	69	77	72	68	74	70	66	71	68	65	63
3	82	72	64	58	79	70	63	58	68	62	57	65	60	56	63	58	55	53
4	75	64	55	49	73	62	55	49	60	53	48	58	52	48	56	51	47	45
5	69	57	49	42	67	56	48	42	54	47	42	52	46	41	50	45	41	39
6	64	51	43	37	62	50	43	37	49	42	36	47	41	36	46	40	36	34
7	59	46	38	33	57	46	38	33	44	37	32	43	37	32	42	36	32	30
8	55	42	35	29	53	42	34	29	41	34	29	39	33	29	38	33	29	27
9	51	39	31	26	50	38	31	26	37	31	26	36	30	26	35	30	26	24
10	48	36	29	24	47	36	29	24	35	28	24	34	28	24	33	27	24	22

Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture
0-30	4244	24.8	27.2
0-40	6874	40.2	44.0
0-60	12002	70.2	76.9
0-90	15606	91.3	100.0
0-180	15606	91.3	100.0

Luminance Data

Angle in Deg	Average 0-Deg cd/sm	Average 45-Deg cd/sm	Average 90-Deg cd/sm
45	12912	11262	10475
55	12415	10124	10353
65	11598	10122	12116
75	9879	11148	10587
85	4975	7027	5821

Modular F-Bay Power Supply Option

Cooper Lighting's F-Bay Modular Power Supply option is available for use with all F-Bay products. The modular power supply allows external fixture access for safe and easy servicing. There is no need to remove lamps or reflectors to disconnect fixture power with F-Bay Modular Power Supply. Access to the individual fixture's power supply allows servicing without turning off all the fixtures, disrupting occupants. F-Bay Modular Power Supply is a time-saver in installation – **simply plug & power.**




1. Modular Power Supply Receptacle supplied mounted into fixture Access Plate
2. Modular Power Cord & Plugs in 120, 277, 347, & 480V configurations for easy plug & power into existing supply

No internal fixture access required for installation or disconnecting power

Modular Motion Sensor Option supplied with Mounting Box and Modular Power Supply Receptacle

Code Compliance

- UL/cUL Certified for Make/Break under load (UL2549)
- Meets NEC requirements for ballast disconnect (NEC 410.73G)
- Allows for addition of Occupancy Sensor without hard connections
- Receptacles complete with insulating/dust cap



**HBI-632-N-UNV-EBT2-UPL**  
 Electronic Ballasts  
 (6) 32WT8 Lamps  
 2850 lumens  
 Spacing criterion:  
 (H) 1.0 x mounting  
 height, (L) 1.1 x  
 mounting height  
 Efficiency 94.5%  
 Test Report:  
 HBI632-UPL.IES  
 LER =FL84  
 Yearly Cost of 1000  
 lumens, 3000 hrs at  
 .08 KWH = \$2.85

Candela				
Angle	Along H	45°	Across L	
0	6096	6096	6096	
5	6103	6109	6097	
10	6057	6018	5933	
15	5952	5772	5528	
20	5776	5383	5054	
25	5542	4954	4556	
30	5252	4442	4306	
35	4916	4027	4025	
40	4529	3719	3653	
45	4117	3379	3251	
50	3665	2969	2984	
55	3186	2542	2597	
60	2686	2231	2288	
65	2169	1823	2045	
70	1634	1539	1588	
75	1105	1147	1089	
80	602	660	616	
85	174	218	158	
90	5	6	7	

Coefficients of Utilization

rc rw RCR	Effective floor cavity reflectance 20%																	
	80%				70%				50%				10%					
	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
0	112	112	112	112	109	109	109	109	103	103	103	98	98	98	93	93	93	91
1	102	98	94	90	99	95	91	88	90	87	85	86	84	82	82	80	78	76
2	93	85	79	73	90	83	77	72	79	74	70	75	71	68	72	69	66	64
3	85	75	67	61	82	73	66	60	70	64	59	67	62	57	64	60	56	54
4	78	66	58	52	75	65	57	51	62	55	50	59	54	49	57	52	48	46
5	71	59	51	45	69	58	50	44	56	49	44	54	47	43	51	46	42	40
6	66	54	45	39	64	52	45	39	50	43	38	49	42	38	47	41	37	35
7	61	49	40	35	59	48	40	34	46	39	34	44	38	33	43	37	33	31
8	57	44	37	31	55	44	36	31	42	35	30	41	35	30	39	34	30	28
9	53	41	33	28	52	40	33	28	39	32	28	38	32	27	36	31	27	25
10	50	38	30	25	49	37	30	25	36	30	25	35	29	25	34	28	25	23

Zonal Lumen Summary


Zone	Lumens	%Lamp	%Fixture
0-30	4812	26.4	27.9
0-40	7183	42.0	44.5
0-60	12252	71.7	75.8
0-90	15556	91.0	96.3
0-180	16155	94.5	100.0

Luminance Data

Angle in Deg	Average 0-Deg cd/sm	Average 45-Deg cd/sm	Average 90-Deg cd/sm
45	13013	10680	10276
55	12415	9905	10120
65	11471	9641	10815
75	9542	9905	9404
85	4462	5590	4052

ORDERING INFORMATION

SAMPLE NUMBER: HBI-632-N-UNV-EB82/PLUS-MP-UPL-U Includes V Hangers for rapid installation<sup>(6)</sup>




NOTES: <sup>(1)</sup>Requires use of MC\_ or MPC\_cord accessories, specify voltage for plugs. <sup>(2)</sup>Voltage must be specified when ordered with plugs or emergency ballasts. <sup>(3)</sup>ER8 and EB8 ballast systems suitable for operation in ambient environments up to 122°F (50°C) in open upright configuration. <sup>(4)</sup>When ordering MS option, specify UNV (for 120 or 277V), 347 or 480V. <sup>(5)</sup>2/3 lamp ballast configurations in EB8/PLUS only for T8 UNC versions. <sup>(6)</sup>Can be used in high abuse applications such as gymnasiums. <sup>(7)</sup>Dimming ballast must be specified at time of order. <sup>(8)</sup>Two required. <sup>(9)</sup>Cannot be combined with Modular Power Receptacle (MP). <sup>(10)</sup>For MWS with MP, choose MP in fixture logic and then choose MWS accessory such as MDS6. <sup>(11)</sup>Recommend Program Rapid Start Ballast when using MS option.



Quick Ship Ordering Information Sample Number: HBI632-MP-UPL-L5

Quick Ship orders ship in 5 days in order quantities not to exceed 200 pieces. Includes V Hangers for rapid installation<sup>(6)</sup>  
NOTE: Orders received after noon are entered on the following day.



NOTES: <sup>(9)</sup>Recommended when utilizing Motion Sensor option. <sup>(10)</sup>Requires use of Modular cord and plug accessories. <sup>(11)</sup>High lumen (3100 initial) lamps supplied for 4100K.

SHIPPING DATA

Catalog No. HBI-632-UPL  
Wt. 16 lbs.



Eaton  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.eaton.com/lighting

Specifications and dimensions subject to change without notice.

## DESCRIPTION

The HBI series is an outstanding solution for high mounting height industrial or retail applications. The HBI optic has been optimized to provide maximum performance from T8 lamps. Optional uplight component is provided to enable excellent ceiling uniformity. HBI's high lumen package allows the benefits of fluorescent to be applied at high mounting heights that were traditionally exclusive to H.I.D. The primary benefits include exceptional color rendering, high system efficacy, 95% lumen maintenance, long lamp life, instant on/instant re-strike, economical dimming, and uniform brightness control. Primary applications include retail, shopping malls, light industrial, gymnasiums and recreational environments.

## SPECIFICATION FEATURES

### Construction

Full bodied steel housing with integral ballast channel adds strength, rigidity and structural protection for optical assembly.

### Electrical

The HBI comes with a standard Class P electronic ballast and twistlock lampholders. UL/cUL listed for high ambient environments up to 55°C (131°F) for all lamps and ballast combinations when used in open upright configurations. Suitable for damp locations. Optional modular power receptacle meets UL2459 and NEC 410.73 and is UL/cUL rated for make and break under load from outside the luminaire to speed maintenance.

### Finish

White enamel finish preceded by a multistage cleaning cycle, iron phosphate coating with rust inhibitor to protect against contaminants and oxidation.

### Downlight/Uplight Optics

Die formed, segmented optical design optimizes performance across three distributions. Optical choices include a narrow distribution for aisles, medium distribution for assembly and loading areas, or wide distribution for general, open area lighting. An uplight option is offered to permit ceiling uniformity and allow for ample lamp and luminaire heat dissipation. Gasketed door frame & lens assembly is optional for more demanding environments.

Catalog #

Type

Project

Comments

Date

Prepared by

### Options

Integral Occupancy Sensor available and provides from 600 sq. ft. (MS) up to 1250 sq. ft. (MSO) of coverage in a maximum mounting height of 40' using interchangeable lens caps provided.

### Mounting

The HBI series is suited for suspension mounting with optional wire hook and chain set or cable mounting. Single monopoint mounting is available with SPM Tong Hanger.

### Warranty

When operated in high ambient conditions, the HBI is supported by a 5 yr/55°C and 3 yr/65°C ballast warranty when used with a high power factor ballast in open, upright configurations. To maximize your warranty, the HBI should be ordered with a high power factor ballast in ambient environments that typically exceed 40°C (102°F).



## HBI SERIES

6 T8 LAMPS

High-Bay Industrial  
Fluorescent Luminaire



## ENERGY DATA

Input Watts:

**EB Ballast**  
632=169W

**EB/Plus Ballast**  
632=218W

**ER Ballast**  
632=169W

**ER/Plus Ballast**  
632=218W

Luminaire Efficacy Rating

**LER = FL-84** (Narrow Beam)

**Catalog Number:** HBI-632-N-UPL

**Yearly Cost of 1000 lumens,**  
3000 hrs at .08 KWH = \$2.85

\*Reference the lamp/ballast data in the  
Technical Section for specific lamp/ballast  
requirements.

\*\*Consult Pre Sales Technical Support.


**LAMPS CONTAIN MERCURY. DISPOSE ACCORDING  
TO LOCAL, STATE OR FEDERAL LAWS**

**LINEAR DISCONNECT**


Safe and convenient means of  
disconnecting power.

ADF091043


2016-07-12 14:50:46




## LAMP CONFIGURATIONS



## DIMENSION TOP VIEW



PHOTOMETRICS



**HBI-632-N-UNV-EB82**  
 Electronic Ballasts  
 (6) 32WT8 Lamps  
 2850 lumens  
 Spacing criterion:  
 (H) 1.3 x mounting  
 height, (L) 1.1 x  
 mounting height  
 Efficiency 91.3%  
 Test Report:  
 HBI632.IES  
 LER =FL81  
 Yearly Cost of 1000  
 lumens, 3000 hrs at  
 .08 KWH = \$2.95

Candela				
Angle	Along H	45°	Across L	
0	5981	5981	5981	
5	6000	5958	5900	
10	5959	5716	5516	
15	5861	5330	4953	
20	5702	4832	4572	
25	5468	4418	4452	
30	5189	4191	4398	
35	4862	3996	4222	
40	4491	3834	3894	
45	4085	3563	3314	
50	3649	3169	2953	
55	3186	2598	2657	
60	2699	2220	2469	
65	2193	1914	2291	
70	1668	1693	1766	
75	1144	1291	1226	
80	635	760	703	
85	194	274	227	
90	10	14	14	

Coefficients of Utilization

rc	Effective floor cavity reflectance																	
	80%				70%				50%				10%					
	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
0	109	109	109	109	106	106	106	106	101	101	101	97	97	97	93	93	93	91
1	99	94	90	87	96	92	89	85	89	85	83	85	82	80	82	80	78	76
2	90	82	76	70	87	80	74	69	77	72	68	74	70	66	71	68	65	63
3	82	72	64	58	79	70	63	58	68	62	57	65	60	56	63	58	55	53
4	75	64	55	49	73	62	55	49	60	53	48	58	52	48	56	51	47	45
5	69	57	49	42	67	56	48	42	54	47	42	52	46	41	50	45	41	39
6	64	51	43	37	62	50	43	37	49	42	36	47	41	36	46	40	36	34
7	59	46	38	33	57	46	38	33	44	37	32	43	37	32	42	36	32	30
8	55	42	35	29	53	42	34	29	41	34	29	39	33	29	38	33	29	27
9	51	39	31	26	50	38	31	26	37	31	26	36	30	26	35	30	26	24
10	48	36	29	24	47	36	29	24	35	28	24	34	28	24	33	27	24	22

Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture
0-30	4244	24.8	27.2
0-40	6874	40.2	44.0
0-60	12002	70.2	76.9
0-90	15606	91.3	100.0
0-180	15606	91.3	100.0

Luminance Data

Angle in Deg	Average 0-Deg cd/sm	Average 45-Deg cd/sm	Average 90-Deg cd/sm
45	12912	11262	10475
55	12415	10124	10353
65	11598	10122	12116
75	9879	11148	10587
85	4975	7027	5821

Modular F-Bay Power Supply Option

Cooper Lighting's F-Bay Modular Power Supply option is available for use with all F-Bay products. The modular power supply allows external fixture access for safe and easy servicing. There is no need to remove lamps or reflectors to disconnect fixture power with F-Bay Modular Power Supply. Access to the individual fixture's power supply allows servicing without turning off all the fixtures, disrupting occupants. F-Bay Modular Power Supply is a time-saver in installation – **simply plug & power.**




1. Modular Power Supply Receptacle supplied mounted into fixture Access Plate
2. Modular Power Cord & Plugs in 120, 277, 347, & 480V configurations for easy plug & power into existing supply

No internal fixture access required for installation or disconnecting power

Modular Motion Sensor Option supplied with Mounting Box and Modular Power Supply Receptacle

Code Compliance

- UL/cUL Certified for Make/Break under load (UL2549)
- Meets NEC requirements for ballast disconnect (NEC 410.73G)
- Allows for addition of Occupancy Sensor without hard connections
- Receptacles complete with insulating/dust cap



**HBI-632-N-UNV-EBT2-UPL**  
 Electronic Ballasts  
 (6) 32WT8 Lamps  
 2850 lumens  
 Spacing criterion:  
 (H) 1.0 x mounting  
 height, (L) 1.1 x  
 mounting height  
 Efficiency 94.5%  
 Test Report:  
 HBI632-UPL.IES  
 LER =FL84  
 Yearly Cost of 1000  
 lumens, 3000 hrs at  
 .08 KWH = \$2.85

Candela				
Angle	Along H	45°	Across L	
0	6096	6096	6096	
5	6103	6109	6097	
10	6057	6018	5933	
15	5952	5772	5528	
20	5776	5383	5054	
25	5542	4954	4556	
30	5252	4442	4306	
35	4916	4027	4025	
40	4529	3719	3653	
45	4117	3379	3251	
50	3665	2969	2984	
55	3186	2542	2597	
60	2686	2231	2288	
65	2169	1823	2045	
70	1634	1539	1588	
75	1105	1147	1089	
80	602	660	616	
85	174	218	158	
90	5	6	7	

Coefficients of Utilization

rc	Effective floor cavity reflectance																	
	80%				70%				50%				10%					
	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
0	112	112	112	112	109	109	109	109	103	103	103	98	98	98	93	93	93	91
1	102	98	94	90	99	95	91	88	90	87	85	86	84	82	82	80	78	76
2	93	85	79	73	90	83	77	72	79	74	70	75	71	68	72	69	66	64
3	85	75	67	61	82	73	66	60	70	64	59	67	62	57	64	60	56	54
4	78	66	58	52	75	65	57	51	62	55	50	59	54	49	57	52	48	46
5	71	59	51	45	69	58	50	44	56	49	44	54	47	43	51	46	42	40
6	66	54	45	39	64	52	45	39	50	43	38	49	42	38	47	41	37	35
7	61	49	40	35	59	48	40	34	46	39	34	44	38	33	43	37	33	31
8	57	44	37	31	55	44	36	31	42	35	30	41	35	30	39	34	30	28
9	53	41	33	28	52	40	33	28	39	32	28	38	32	27	36	31	27	25
10	50	38	30	25	49	37	30	25	36	30	25	35	29	25	34	28	25	23

Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture
0-30	4812	26.4	27.9
0-40	7183	42.0	44.5
0-60	12252	71.7	75.8
0-90	15556	91.0	96.3
0-180	16155	94.5	100.0


Luminance Data

Angle in Deg	Average 0-Deg cd/sm	Average 45-Deg cd/sm	Average 90-Deg cd/sm
45	13013	10680	10276
55	12415	9905	10120
65	11471	9641	10815
75	9542	9905	9404
85	4462	5590	4052



ORDERING INFORMATION

SAMPLE NUMBER: HBI-632-N-UNV-EB82/PLUS-MP-UPL-U Includes V Hangers for rapid installation<sup>(6)</sup>




NOTES: <sup>(1)</sup>Requires use of MC\_ or MPC\_cord accessories, specify voltage for plugs. <sup>(2)</sup>Voltage must be specified when ordered with plugs or emergency ballasts. <sup>(3)</sup>ER8 and EB8 ballast systems suitable for operation in ambient environments up to 122°F (50°C) in open upright configuration. <sup>(4)</sup>When ordering MS option, specify UNV (for 120 or 277V), 347 or 480V. <sup>(5)</sup>2/3 lamp ballast configurations in EB8/PLUS only for T8 UNC versions. <sup>(6)</sup>Can be used in high abuse applications such as gymnasiums. <sup>(7)</sup>Dimming ballast must be specified at time of order. <sup>(8)</sup>Two required. <sup>(9)</sup>Cannot be combined with Modular Power Receptacle (MP). <sup>(10)</sup>For MWS with MP, choose MP in fixture logic and then choose MWS accessory such as MDS6. <sup>(11)</sup>Recommend Program Rapid Start Ballast when using MS option.



Quick Ship Ordering Information Sample Number: HBI632-MP-UPL-L5

Quick Ship orders ship in 5 days in order quantities not to exceed 200 pieces. Includes V Hangers for rapid installation<sup>(6)</sup>  
NOTE: Orders received after noon are entered on the following day.



NOTES: <sup>(8)</sup>Recommended when utilizing Motion Sensor option. <sup>(10)</sup>Requires use of Modular cord and plug accessories. <sup>(11)</sup>High lumen (3100 initial) lamps supplied for 4100K.

SHIPPING DATA

Catalog No. HBI-632-UPL  
Wt. 16 lbs.



Eaton  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.eaton.com/lighting

Specifications and dimensions subject to change without notice.