



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GHQ1020 20A 277 Volt 14 Ka *Eaton Corp*

Catalog Number	GHQ1020
Manufacturer	Eaton Corp
Description	Eaton GHQ Thermal Magnetic Circuit Breaker, Thermal-Magnetic Circuit Breaker, 20 A, 14 Kaic, Single-Pole, 277 V, Non-Interchangeable, GHP, GDB-Frame, 120/208/240 V Shunt Trip
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole

### Features

dimensions	2.9000 IN X 1.0000 IN X 2.9000 IN
interrupt rating	14 kAIC
Poles	1
Trip Type	Non-Interchangeable
Voltage Rating	277V

### Descriptions

Description	20A 277 VOLT 14 KA
extra long description	ETN GHQ1020 20 Amp 277 Volt 14 Ka
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton GHQ thermal magnetic circuit breaker, Thermal-magnetic circuit breaker, 20 A, 14 kAIC, Single-pole, 277 V, Non-Interchangeable, GHP, GDB-Frame, 120/208/240 V Shunt trip
Product Type	20 Amp 277 Volt 14 Ka

### Manufacturer Information

Brand	Eaton
GTIN	00782114985113
Manufacturers Part Number	GHQ1020
UPC	782114985113

### Taxonomies, Classifications, and Categories

Type	Thermal magnetic circuit breakers
------	-----------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	24
Weight Per each	0.35

## Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative Energy
standard	UL 489