



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GMA3R 3A 250V Fa 5X20MM Glass Fuse

Bussmann Fuses

Catalog Number	GMA3R
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, 60 Min @ 135%;2 Min @ 200 % Response Time, Ferrule End X Ferrule End Connection, 3 A, 250 V Ac, Glass (Body);Brass(End Cap) Material, Ferrule Terminal, 5.2 MM Diameter, 20 MM Overall Length
Weight per unit	0.0050 (lbs/each)
Product Category	Small Dimension Fuses

Descriptions

Description	3A 250V FA 5X20MM GLASS FUSE
extra long description	BUSS GMA-3-R GMA 3A BUSS FUSE
Features	Fast-acting, glass tube 5 mm x 20 mm ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block or fuse clip. Also available with axial leads for thru-hole installation Eaton's GMA fast-acting, glass tube 5mm x 20mm ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available

Manufacturer Information

Brand	Eaton
GTIN	00051712647946
UPC	051712647946

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
----------------------	---------------------------

Packaging

Carton	5
Weight Per each	0.005