



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GUAT14 1/2" Guat Cond CVR&GSK

Crouse-Hinds

Catalog Number	GUAT14
Manufacturer	Crouse-Hinds
Description	Conduit Outlet Box With Cover, ElectroGalvanized and Aluminum Acrylic Paint (Body);Natural (Cover), T Body Type, 1/2 In Trade Size, Threaded Connection, Round, 3 In (Cover) Opening Size, 3 Hubs, 1/2 In Hub Size, (3) Side Hub Location, T Configuration, 2-1/2 In Width, 1-13/16 In Height, (4) Pad, 1.85 LB/Ea
Weight per unit	1.9 (lbs/each)
Product Category	Bodies & Covers

Features

Cable Entry dimensions	(3) Side 4.2500 IN X 2.2500 IN X 3.3800 IN
------------------------	---

Dimensions and Weight

Size	1/2 in
------	--------

Descriptions

Construction	Explosionproof, Dust-Ignitionproof, Raintight
Description	1/2" GUAT COND CVR&GSK
extra long description	CRS-H GUAT14 1/2 OUTLET BX 2 CVR FO
Features	Crouse-Hinds series GUA and GUR explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes. GUA and GUR outlet boxes are certified for Class I, Division 1, Groups B, C, D and Class II, Division 1, Groups E, F, G. GUA boxes are available in ten different hub arrangements, maximizing flexibility in th

Manufacturer Information

Brand	Eaton
GTIN	00782274467207
UPC	782274467207

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	2
Weight Per each	1.85

Uses, Certifications, and Standards

standard	UL 886, CSA C22.2
----------	-------------------