



Safety Data Sheet

Copyright, 2018, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	19-9776-6	Version Number:	8.04
Issue Date:	07/26/18	Supersedes Date:	06/29/18

SECTION 1: Identification

1.1. Product identifier

3M FireBarrier™ Sealant IC 15 WB+

Product Identification Numbers

42-0016-4768-6, 42-0016-4769-4, 42-0016-4770-2, 98-0400-5509-1, 98-0400-5510-9, 98-0400-5511-7, 98-0400-5512-5, 98-0400-5630-5

1.2. Recommended use and restrictions on use

Recommended use

Fire Barrier Sealant.

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Industrial Adhesives and Tapes Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Reproductive Toxicity: Category 2.

2.2. Label elements

Signal word

Warning

Symbols

Health Hazard |

Pictograms

**Hazard Statements**

Suspected of damaging fertility or the unborn child.

Precautionary Statements**General:**

Keep out of reach of children.

Prevention:

Obtain special instructions before use.

Do not handle until all safety precautions have been read and understood.

Wear protective gloves.

Response:

IF exposed or concerned: Get medical advice/attention.

Storage:

Store locked up.

Disposal:

Dispose of contents/container in accordance with applicable local/regional/national/international regulations.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Calcium Carbonate	1317-65-3	30 - 60 Trade Secret *
Water	7732-18-5	10 - 30 Trade Secret *
Polymer NJTS Reg. No. 04499600-7314	Trade Secret*	10 - 30 Trade Secret *
Zinc Borate 2335	138265-88-0	3 - 7 Trade Secret *
Sodium Silicate	1344-09-8	3 - 7 Trade Secret *
2-Aminoisobutanol	124-68-5	< 0.5 Trade Secret *
Quartz Silica	14808-60-7	< 0.5 Trade Secret *

NJTS or NJTSRN: New Jersey Trade Secret Registry Number.

*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

SECTION 4: First aid measures

4.1. Description of first aid measures**Inhalation:**

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Wash with soap and water. If you are concerned, get medical advice.

Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

If Swallowed:

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures

5.1. Suitable extinguishing media

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products

Substance

Carbon monoxide
Carbon dioxide

Condition

During Combustion
During Combustion

5.3. Special protective actions for fire-fighters

Wear full protective clothing, including helmet, self-contained, positive pressure or pressure demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Clean up residue. Seal the container. Dispose of collected material as soon as possible in accordance with applicable local/regional/national/international regulations.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep out of reach of children. Do not handle until all safety precautions have been read and understood. Avoid breathing dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Avoid release to the environment. Use personal protective equipment (gloves, respirators, etc.) as required.

7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
Calcium Carbonate	1317-65-3	OSHA	TWA(as total dust):15 mg/m ³ ;TWA(respirable fraction):5 mg/m ³	
Quartz Silica	14808-60-7	ACGIH	TWA(respirable fraction):0.025 mg/m ³	A2: Suspected human carcin.
Quartz Silica	14808-60-7	OSHA	TWA Table Z-1(respirable):0.05 mg/m ³ ;TWA Table Z-3(respirable):0.1 mg/m ³	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

8.2. Exposure controls

8.2.1. Engineering controls

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

None required.

Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing.

Gloves made from the following material(s) are recommended: Nitrile Rubber

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapors and particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form:	Solid
Specific Physical Form:	Paste
Odor, Color, Grade:	Light yellow viscous paste with a mild odor
Odor threshold	<i>No Data Available</i>
pH	8 - 9
Melting point	<i>No Data Available</i>
Boiling Point	<i>Not Applicable</i>
Flash Point	Flash point > 93 °C (200 °F)
Evaporation rate	<i>No Data Available</i>
Flammability (solid, gas)	Not Classified
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>
Vapor Pressure	<i>No Data Available</i>
Vapor Density	<i>No Data Available</i>
Density	1.4 g/cm ³
Specific Gravity	1.4 [Ref Std: WATER=1]
Solubility in Water	Moderate
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	<i>No Data Available</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	<i>No Data Available</i>
Molecular weight	<i>No Data Available</i>
Volatile Organic Compounds	<=20 % weight [Test Method: tested per EPA method 24]
VOC Less H₂O & Exempt Solvents	<=4 g/l [Test Method: tested per EPA method 24]

SECTION 10: Stability and reactivity**10.1. Reactivity**

This material is considered to be non reactive under normal use conditions.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

None known.

10.5. Incompatible materials

None known.

10.6. Hazardous decomposition products**Substance**

None known.

Condition

Refer to section 5.2 for hazardous decomposition products during combustion.

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

May cause additional health effects (see below).

Skin Contact:

Contact with the skin during product use is not expected to result in significant irritation.

Eye Contact:

Contact with the eyes during product use is not expected to result in significant irritation.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May cause additional health effects (see below).

Additional Health Effects:

Reproductive/Developmental Toxicity:

Contains a chemical or chemicals which can cause birth defects or other reproductive harm.

Carcinogenicity:

Ingredient	CAS No.	Class Description	Regulation
SILICA, CRYSTAL AIRRESP	14808-60-7	Known human carcinogen	National Toxicology Program Carcinogens
Quartz Silica	14808-60-7	Grp. 1: Carcinogenic to humans	International Agency for Research on Cancer

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Calcium Carbonate	Dermal	Rat	LD50 > 2,000 mg/kg
Calcium Carbonate	Inhalation-Dust/Mist (4 hours)	Rat	LC50 3 mg/l
Calcium Carbonate	Ingestion	Rat	LD50 6,450 mg/kg
Polymer NJTS Reg. No. 04499600-7314	Dermal		LD50 estimated to be > 5,000 mg/kg
Polymer NJTS Reg. No. 04499600-7314	Ingestion	Rat	LD50 > 2,000 mg/kg
Zinc Borate 2335	Dermal	Rabbit	LD50 > 5,000 mg/kg
Zinc Borate 2335	Inhalation-	Rat	LC50 > 4.95 mg/l

	Dust/Mist		
Zinc Borate 2335	Ingestion	Rat	LD50 > 5,000 mg/kg
Sodium Silicate	Dermal	Rabbit	LD50 > 4,640 mg/kg
Sodium Silicate	Ingestion	Rat	LD50 500 mg/kg
2-Aminoisobutanol	Dermal	Rabbit	LD50 > 2,000 mg/kg
2-Aminoisobutanol	Ingestion	Rat	LD50 2,900 mg/kg
Quartz Silica	Dermal		LD50 estimated to be > 5,000 mg/kg
Quartz Silica	Ingestion		LD50 estimated to be > 5,000 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
Calcium Carbonate	Rabbit	No significant irritation
Polymer NJTS Reg. No. 04499600-7314	Rabbit	Minimal irritation
Zinc Borate 2335	Rabbit	No significant irritation
Sodium Silicate	Rabbit	Corrosive
2-Aminoisobutanol	Rabbit	Irritant
Quartz Silica	Professional judgement	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
Calcium Carbonate	Rabbit	No significant irritation
Polymer NJTS Reg. No. 04499600-7314	Professional judgement	Mild irritant
Zinc Borate 2335	Rabbit	Severe irritant
Sodium Silicate	Rabbit	Corrosive
2-Aminoisobutanol	Rabbit	Corrosive

Skin Sensitization

Name	Species	Value
Zinc Borate 2335	Guinea pig	Not classified
Sodium Silicate	Mouse	Not classified
2-Aminoisobutanol	Guinea pig	Not classified

Respiratory Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
Zinc Borate 2335	In Vitro	Some positive data exist, but the data are not sufficient for classification
Sodium Silicate	In Vitro	Not mutagenic
Sodium Silicate	In vivo	Not mutagenic
2-Aminoisobutanol	In Vitro	Not mutagenic
2-Aminoisobutanol	In vivo	Not mutagenic
Quartz Silica	In Vitro	Some positive data exist, but the data are not sufficient for classification
Quartz Silica	In vivo	Some positive data exist, but the data are not sufficient for classification

Carcinogenicity

Name	Route	Species	Value
Quartz Silica	Inhalation	Human and animal	Carcinogenic

Reproductive Toxicity

Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
Calcium Carbonate	Ingestion	Not classified for development	Rat	NOAEL 625 mg/kg/day	prematuring & during gestation
Zinc Borate 2335	Ingestion	Toxic to male reproduction	Rat	NOAEL 100 mg/kg/day	92 days
Zinc Borate 2335	Ingestion	Toxic to development	Rat	LOAEL 100 mg/kg/day	during gestation
Sodium Silicate	Ingestion	Not classified for development	Mouse	NOAEL 200 mg/kg/day	during gestation
2-Aminoisobutanol	Ingestion	Not classified for female reproduction	Rat	NOAEL 1,000 mg/kg/day	prematuring into lactation
2-Aminoisobutanol	Ingestion	Not classified for male reproduction	Rat	NOAEL 1,000 mg/kg/day	37 days
2-Aminoisobutanol	Dermal	Not classified for development	Rat	NOAEL 300 mg/kg/day	during gestation
2-Aminoisobutanol	Ingestion	Toxic to development	Rat	NOAEL 100 mg/kg/day	prematuring into lactation

Target Organ(s)

Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Calcium Carbonate	Inhalation	respiratory system	Not classified	Rat	NOAEL 0.812 mg/l	90 minutes
Zinc Borate 2335	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	similar health hazards	NOAEL Not available	
Sodium Silicate	Inhalation	respiratory irritation	May cause respiratory irritation	official classification	NOAEL Not available	
2-Aminoisobutanol	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	Mouse	NOAEL Not available	

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Calcium Carbonate	Inhalation	respiratory system	Not classified	Human	NOAEL Not available	occupational exposure
Zinc Borate 2335	Inhalation	immune system respiratory system heart endocrine system hematopoietic system liver nervous system kidney and/or bladder	Not classified	Rat	NOAEL 0.15 mg/l	2 weeks
Zinc Borate 2335	Ingestion	endocrine system liver kidney and/or bladder heart skin bone, teeth, nails, and/or hair hematopoietic	Not classified	Rat	NOAEL 375 mg/kg/day	92 days

		system immune system nervous system eyes respiratory system vascular system				
Sodium Silicate	Ingestion	kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	Dog	LOAEL 2,400 mg/kg/day	4 weeks
Sodium Silicate	Ingestion	endocrine system blood	Not classified	Rat	NOAEL 804 mg/kg/day	3 months
Sodium Silicate	Ingestion	heart liver	Not classified	Rat	NOAEL 1,259 mg/kg/day	8 weeks
2-Aminoisobutanol	Ingestion	liver	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 23 mg/kg/day	90 days
2-Aminoisobutanol	Ingestion	blood eyes kidney and/or bladder	Not classified	Dog	NOAEL 2.8 mg/kg/day	1 years
Quartz Silica	Inhalation	silicosis	Causes damage to organs through prolonged or repeated exposure	Human	NOAEL Not available	occupational exposure

Aspiration Hazard

For the component/components, either no data are currently available or the data are not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

Ecotoxicological information

<u>Test Organism</u>	<u>Test Type</u>	<u>Result</u>
Water flea, Daphnia magna	48 hours Aquatic Toxicity - Acute	27 mg/l
Green algae, Pseudokirchneriella subcapitata	72 hours Aquatic Toxicity - Chronic	2.6 % weight

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Dispose of waste product in a permitted industrial waste facility. As a disposal alternative, incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information**15.1. US Federal Regulations**

Contact 3M for more information.

EPCRA 311/312 Hazard Classifications:**Physical Hazards**

Not applicable

Health Hazards

Reproductive toxicity

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
Zinc Borate 2335 (ZINC COMPOUNDS)	138265-88-0	3 - 7

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

The components of this material are in compliance with the provisions of Australia National Industrial Chemical Notification and Assessment Scheme (NICNAS). Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the new substance notification requirements of CEPA.

The components of this material are in compliance with the China "Measures on Environmental Management of New Chemical Substance". Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of the Korean Toxic Chemical Control Law. Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the chemical notification requirements of TSCA.

This product complies with the New Zealand Hazardous Substances and New Organisms Act (1996).

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information**NFPA Hazard Classification**

Health: 1 **Flammability:** 1 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include

the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Document Group:	19-9776-6	Version Number:	8.04
Issue Date:	07/26/18	Supersedes Date:	06/29/18

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M.

3M USA SDSs are available at www.3M.com