

# e-Vision Low Wattage 20-150W

## E-VISION ELE MH BAL 100W M140 120-277V 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

### Product data


General Information		Input Current (Operating) (Min)	
ANSI Code	C90-M90,M140,C191		0.4 A
Lamp Type	100W MH	Input Power (Nom)	110-109 W
Number of Lamps	1 piece/unit	Rated Lamp Watts	100 W
Ballast Type	Electronic HID	<b>Wiring</b>	
Base Model	IMH100DBLS	Color Input Terminals	No terminals
Suitable For Outdoor Use	Yes	Color Output Terminals	No terminals
<b>Operating and Electrical</b>		Wire Striplength	0.50 mm
Input Voltage	120 to 277 V	Control Wire Gauge	NA
Input Frequency	50 to 60 Hz	Wire Length By Color	All leads = 11"
Max THD	15 %	Wire Gauge (Nom)	18AWG mm
Lamp Current Crest Factor (Nom)	1.8	Wire Type	Stranded
Ignition Time (Nom)	1200 s	Remote Wiring Configuration Allowed	Yes
Ballast Factor (Nom)	1	Tandem Wiring Configuration Allowed	No
Power Factor (Nom)	0.90	Through Wiring Configuration Allowed	No
Input Current (Operating) (Max)	0.92 A	Connector Type	No connector

## e-Vision Low Wattage 20-150W

Temperature	
T-Case Maximum (Nom)	85 °C
Mechanical and Housing	
Housing Material	Metal
Housing	D
Housing Dimensions	4.3" x 3.0" x 1.5"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approbation Marks	CSA certificate UL certificate NOM certificate RoHS Compliant
Sound Rating	A

UL Recognized	No
Product Data	
Order product name	E-VISION IMH100DBLSM
EAN/UPC - Product	781087032213
Order code	IMH100DBLSM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913710288202
Net Weight (Piece)	0.667 kg

### Dimensional drawing



Product	A1	A2	A3	A4	B1	B2	C1
E-VISION IMH100DBLSM	5.0 in	4.3 in	4.6 in	2.0 in	3.0 in	0.7 in	1.5 in

E-VISION IMH100DBLSM

