



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2736 LKG FLG-RCPT, 30A 3P 480V, L16-30R, WH *Hubbell Wiring Devices*

Catalog Number	HBL2736
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 30A 3-Phase Delta 480V Ac, 3-Pole 4-Wire Grounding, L16-30R, Screw Terminal, White
Weight per unit	0.3500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Screw Terminal
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	4-Wire
pallet quantity	1610
Phase	3
Poles	3-Pole
Voltage Rating	3 Phase 480 VAC
Wattage	14,400
Wire Size	#16 to #8

Dimensions and Weight

Size	3.06 in x 3.06 in x 2.27 in
------	-----------------------------

Descriptions

Description	LKG FLG-RCPT, 30A 3P 480V, L16-30R, WH
extra long description	HWK HBL2736 LKG FLG-RCPT, 30A 3P 4
Long Description	Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, L16-30R, Screw Terminal, White
Product Type	LKG FLG-RCPT, 30A 3P 480V, L16-30R, WH
Special Features	Standard

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585039367
Manufacturers Part Number	HBL2736
UPC	783585039367



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Flanged Receptacle

Packaging

Carton	1
Package	10
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L16-30R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498