

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



**Product Type** 

### L15T848GC850DX2G 15W Led T8 48" 50K DBL/SNGL Ended Coated Glass G2 Keystone Technologies

Keystone Technologi	es
Catalog Number	L15T848GC850DX2G
Manufacturer	Keystone Technologies
Description	14.5W Led T8 Tube, Gen 2, Shatter-Proof Coated Glass
	Contruction, 4FT, 5000K, 120-277V Input, 25 PCS Carton, Direct
	Drive, Single or Double Ended Wiring.
Weight per unit	0.6600 (lbs/each)
Product Category	Lighting
Features	
Ballast Type	N/A
beam angle	240
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
Lamp Type	T8
lumens	2000
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	15
Wire Type	N/A
Material, Color, and Finish	
Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A
Descriptions	
Construction	Frosted Shatterproof Glass
Description	15W LED T8 48" 50K DBL/SNGL ENDED COATED GLASS G2
extra long description	Key KT-LED15T8-48GC-850-DX2 /G2 15W
Long Description	14.5W LED T8 Tube, Gen 2, Shatter-Proof Coated Glass
J	

Contruction, 4ft, 5000K, 120-277V Input, 25 pcs Carton, Direct

15W Led T8 Tube, Gen 2, Shatter-Proof Coated Glass Contructi

Drive, Single or Double Ended Wiring.



# Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

n	/lanufac	HILPAR	INTARMA	TION

Brand	Keystone
GTIN	00843654150086
Manufacturers Part Number	KT-LED15T8-48GC-850-DX2 /G2
UPC	843654150086

#### **Taxonomies, Classifications, and Categories**

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR
	LAMPS

#### **Packaging**

Carton	25
Weight Per each	0.66

#### Uses, Certifications, and Standards

Energy Star N	
---------------	--