



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL520C6W PS, IEC, Conn, 4P5W, 16/20A 200-415V, 4X/69K** *Hubbell Wiring Devices*

|                  |  |
|------------------|--|
| Catalog Number   | HBL520C6W  |
| Manufacturer     | Hubbell Wiring Devices   |
| Description      | Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector, 16/20 A, 200/346-240/415 V;220/380-240/415 V, 4-Pole 5-Wire Wire Grounding, Terminal Screws, Red, 4X and Ip69k |
| Weight per unit  | 1.5 (lbs/each)   |
| Product Category | Pin & Sleeve Devices   |

### **Features**

|                      |                                     |
|----------------------|-------------------------------------|
| amperage rating      | 16/20                               |
| connection           | Pressure Screw Terminal             |
| Dielectric Strength  | Withstands 3000V Minimum in         |
| insulation           | Insulated Body                      |
| Material             | Thermoplastic                       |
| Number of Conductors | 5-Wire Grounding                    |
| Number of Wires      | 5-Wire                              |
| Phase                | Multi Phase                         |
| Poles                | 4-Pole                              |
| Voltage Rating       | 200/346-240/415 V;220/380-240/415 V |
| Wire Size            | #14 AWG to #10 AWG                  |

### **Material, Color, and Finish**

|       |     |
|-------|-----|
| Color | Red |
|-------|-----|

### **Dimensions and Weight**

|      |          |
|------|----------|
| Size | Standard |
|------|----------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | PS,IEC,CONN,4P5W,16/20A 200-415V, 4X/69K  |
| extra long description | HWDK HBL520C6W PS,IEC,CONN,4P5W,16/   |
| Features               | Watertight Devices - Hubbell's IEC 60309 Pin and Sleeve plugs, connectors, inlets and receptacles are the highest performing products available. The HBL® series of IEC pin and sleeve were designed for the demanding North American market. Hubbell was the first and is still only manufacturer of IEC 60309 devices in the USA and have numerous innovative features noted below. The IEC line of plugs and connectors are made with a rugged super tough, one-piece housing. The thermoset polyester contact carrier provi |
| Long Description       | Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector, 16/20 A, 200/346-240/415 V;220/380-240/415 V, 4-Pole 5-Wire Wire Grounding, Terminal Screws, Red, 4X and IP69k  |
| Product Type           | PS, IEC, Conn, 4P5W, 16/20A 200-415V, 4X/69K  |
| Special Features       | Watertight  |

## Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | WIRING DEVICE-KELLEMS |
| GTIN                      | 00783585372709        |
| Manufacturers Part Number | HBL520C6W             |
| series                    | HBL Heavy Duty        |
| UPC                       | 783585372709          |

## Taxonomies, Classifications, and Categories

|                      |                           |
|----------------------|---------------------------|
| Category Description | Pin & Sleeve Devices      |
| Type                 | Watertight Connector Body |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 0   |
| Weight Per each | 1.5 |

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | High Ampacity Watertight Connections   |
| environmental conditions | Watertight   |
| Mounting                 | Cord   |
| nema rating              | Non-NEMA   |
| standard                 | CSA Certified File LR280C;UL Classified to IEC 60309-1 IEC 60309-2;UL Listed to UL1682 |