

brighten



The versatile brightness of GE's LED MR16/MRX16 lamps are not just something you see, it's something you feel.

LED MR16/MRX16 lamps

For high-output in decorative lighting applications, GE's dimmable 7-watt LED MR16/MRX16 lamp is the perfect solution.

LOW-COST OPERATION

- For example, using only 7 watts of energy, save over \$118 in energy costs over the rated life of a lamp versus a standard 50-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus halogen MR16/MRX16 light sources

EXCELLENT COLOR RENDERING

- Available with a CRI of 80 - 95

COLOR TEMPERATURE

- Halogen-like color
- Available in 2700K, 3000K and 4000K

LONG LIFE

- Up to 25,000 hours rated life (L70)

DIMMABLE

- Dims from 100% to 10%

BEAM PATTERNS

- Available in 15°, 25° and 35° beam patterns

TRANSFORMER COMPATIBILITY

- A lamp-transformer compatibility table has been developed and is available at www.gelighting.com/LED-MR16

ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

GE QUALITY AND RELIABILITY

- 3-year limited warranty

To learn more about saving money and energy, go to: gelighting.com/ThinkLED

When you Think LED lighting, Think GE.

ecomaginationSM






imagination at work

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LED MR16/MRX16 lamps

Directional Lamps (MR16/MRX16)

Bulb Shape	Base Type	Watts	Order Code	Description	Case Volts	MOL Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
12 Volt AC/DC MR16																		
	GU5.3	7	93412	LED7DMR16S830/15	12	6	2.3	460	3800	3000	80	35W	25,000	Yes	★	Damp	Accent, 15° beam, Silver	
			69920	LED7DMR16D830/25	12	6	1.9	390	1900	3000	83	35W	25,000	Yes	★	Damp	Accent, 25° beam, Silver	
			93433	LED7DMR16S840/15	12	6	1.97	490	4200	4000	80	35W	25,000	Yes	★	Damp	Accent, 15° beam, Silver	
			39351	LED7DMRX16830/35	12	6	1.97	420	1100	3000	82	35W	25,000	Yes	★	Damp	Accent, 35° beam, White	
	GU5.3	7	35196	LED7XDMRX1683025	12	6	2.2	500	1350	3000	80	50W	25,000	Yes	★	Damp	Accent, 35° beam, White	
			35206	LED7XDMRX1682725	12	6	2.2	480	2350	2700	80	50W	25,000	Yes	★	Damp	Accent, 25° beam, White	
			39360	LED7XDMRX16827/25	12	6	2.2	400	1800	2700	80	35W	25,000	Yes	★	Damp	Accent, 25° beam, White	
			35195	LED7XDMRX1683025	12	6	2.2	500	2350	3000	80	50W	25,000	Yes	★	Damp	Accent, 25° beam, White	
			35196	LED7XDMRX1683035	12	6	2.2	500	1350	3000	80	50W	25,000	Yes	★	Damp	Accent, 35° beam, White	
			35206	LED7XDMRX1682725	12	6	2.2	480	2350	2700	80	50W	25,000	Yes	★	Damp	Accent, 25° beam, White	
			35214	LED7XDMRX1682735	12	6	2.2	480	1350	2700	80	50W	25,000	Yes	★	Damp	Accent, 35° beam, White	
			39405	LED7DMRX16827/35	12	6	2.2	400	1000	2700	80	35W	25,000	Yes	★	Damp	Accent, 35° beam, White	
			39408	LED7DMRX16840/25	12	6	2.2	460	2100	4000	83	35W	25,000	Yes	★	Damp	Accent, 25° beam, White	
			21359	LED7MRX16R930/10	12	6	2.01	350	8000	3000	95	50W	25,000	-		Damp	Spot, 10° beam, Reveal	
			Value 12 Volt AC/DC MR16															
	GU5.3	6	35542	LED5.5DMR1684035	12	6	1.8	460	1100	4000	80	35W	25,000	Yes	★	Damp	Accent, 35° beam, White	
			35535	LED5.5DMR1683035	12	6	1.88	420	1000	3000	80	35W	25,000	Yes	★	Damp	Accent, 35° beam, White	
			35540	LED5.5DMR1682735	12	6	1.88	400	1000	2700	80	35W	25,000	Yes	★	Damp	Accent, 35° beam, White	
	7	39483	LED7XDMR16-V8335	12	6	1.88	550	1400	3000	80	50W	25,000	Yes		Damp	Accent, 35° beam, White		
		39542	LED7XDMR16-V2725	12	6	1.88	530	2400	2700	80	50W	25,000	Yes		Damp	Accent, 25° beam, White		
		39567	LED7XDMR16-V2735	12	6	1.88	530	1400	2700	80	50W	25,000	Yes		Damp	Accent, 35° beam, White		
		35543	LED7XDMR16-28325	12	6	1.88	500	2350	3000	80	50W	25,000	Yes	★	Damp	Accent, 25° beam, White		

Get more information at GELighting.com/ThinkLED

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)
 ** Minimum order quantity = 6
 ★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.
 # UL 1993 Environmental Requirements for LED LAMPS
 Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.
 Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.
 Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.
 Notes: 1) Product descriptions ending in "TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.
 2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900



Product is compliant with material restriction requirements of RoHS

ENERGY STAR® is a registered U.S. mark



www.gelighting.com

GE and the GE Monogram are trademarks of the General Electric Company. All other trademarks are the property of their respective owners. Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions. GE Lighting and GE Lighting Solutions, LLC are businesses of the General Electric Company. © 2016 GE.

65027 | Rev 9/13/16