



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LTXES06BB 1-1/2"X50' LT FLX MTLC CNDT

Abb Installation Products, Inc

Catalog Number	LTXES06BB
Manufacturer	Abb Installation Products, Inc
Description	Liquid Tight Flexible Metallic Conduit, Extreme Temperature Range, Galvanised Steel Core With TPR Jacket, Conduit Size 1-1/2 Inch, Length 15 Meters/50 Feet, Working Temperature -60 to 150 Degrees C, Intermitting to 165 Degrees C, Compliant to Rohs, Black
Weight per unit	1.0 (lbs/each)
Product Category	Liquid Tight Conduit

Features

Inside Diameter	1.575
outside diameter	1.9

Material, Color, and Finish

Finish	TPR Jacket
--------	------------

Dimensions and Weight

Length	600
--------	-----

Descriptions

Description	1-1/2"X50' LT FLX MTLC CNDT
extra long description	ABB LTXES06B-B LFMC XTMP 1-1/2 BLK
Features	Extreme temperature, CE compliant Liquid-tight Flexible Metallic Conduits provide excellent performance in extreme low and high temperature environments
Long Description	Liquid Tight Flexible Metallic Conduit, Extreme Temperature Range, Galvanised Steel Core with TPR Jacket, Conduit Size 1-1/2 Inch, Length 15 Meters/50 Feet, Working Temperature -60 to 150 Degrees C, Intermitting to 165 Degrees C, Compliant to RoHS, Black
Product Type	LFMC XTMP 1-1/2 BLK 15M/50FT
Special Features	Designed to meet UL 360 ID/OD dimension requirements

Manufacturer Information

Brand	T&B Liquidtight Systems
GTIN	00786210106779
Manufacturers Part Number	LTXES06B-B
UPC	786210106779

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquid Tight Flexible Metallic Conduit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size 1-1/2 in

Packaging

Carton 50

Weight Per foot 1.04

Uses, Certifications, and Standards

Application Used in extremely high temperature applications such as
commercial ovens and refrigeration, industrial furnaces and
foundries

standard RoHS