



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

NK6PPG24Y CAT6 Flat 24PORT 1RU Punch Patch

Panduit Corporation

Catalog Number	NK6PPG24Y
Manufacturer	Panduit Corporation
Description	The Netkey® Flat Punchdown Keystone Patch Panel Terminates 4-Pair, 22–26 Awg, 100-Ohm Twisted Pair Cable. These Cat 6 Patch Panels Mount to 19" and 23" Racks and Includes 24 Ports. The RJ45 Interface Provides A Quick Plug and Play Connection to RJ45 Patch Cords. This Punchdown Patch Panel Is 1 Ru, Made Of Steel and Is Black.
Weight per unit	2.0 (lbs/each)
Product Category	Wire

Features

connector	NA
Material	CRS
Number of Ports	24

Dimensions and Weight

Depth	1.17
Width	19

Descriptions

Description	CAT6 FLAT 24PORT 1RU PUNCH PATCH
extra long description	PAN NK6PPG24Y Cat 6 Punchdown Keyst
Long Description	The NetKey® Flat Punchdown Keystone Patch Panel terminates 4-pair, 22–26 AWG, 100-ohm twisted pair cable. These Cat 6 patch panels mount to 19" and 23" racks and includes 24 ports. The RJ45 interface provides a quick plug and play connection to RJ45 patch cords. This punchdown patch panel is 1 RU, made of steel and is black.
Product Type	Cat 6 Punchdown Keystone Patch Panel, 24 Port

Manufacturer Information

Brand	PANDUIT
GTIN	00074983055807
Manufacturers Part Number	NK6PPG24Y
UPC	074983055807

Taxonomies, Classifications, and Categories

Category Description	Portable Cords, Voice, Data, Video Wire & Cable
Type	Patch Panel Kit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Packaging

Carton	1
Package	10
Weight Per each	1.98

Uses, Certifications, and Standards

Application	NA
standard	Meets all TIA/EIA-568-C.2 Category 6 and ISO 11801 2nd Edition Class E channel requirements at swept frequencies up to 250 MHz, Meets ANSI/TIA-568-C.2 and ISO 11801 Category 6 component requirements at swept frequencies up to 250 MHz, Complies with ANSI/TI