



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street  
72209-0000, AR Little Rock  
Phone: 501-565-1785  
Fax: 501-565-0827



## **P1014RL Pan-Term® P10-14R-L Ring** *Panduit Corporation*

Catalog Number	P1014RL
Manufacturer	Panduit Corporation
Description	The P10-14R-L Pan-Term® Terminal Is A Non-Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.2600 (lbs/each)
Product Category	Small Terminals & Connectors

### **Features**

connection	Standard
insulation	None
Material	Copper
media	Yes
Voltage Rating	2000
Wire Size	10

### **Material, Color, and Finish**

Finish	Tinned
--------	--------

### **Dimensions and Weight**

Size	1/4"
------	------

### **Descriptions**

Description	PAN-TERM® P10-14R-L RING
extra long description	PAN P10-14R-L Pan-Term® P10-14R-L R
Long Description	The P10-14R-L Pan-Term® Terminal is a non-insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® P10-14R-L Ring Terminal, Bare, 10-14 Awg, 1/4" Stu

### **Manufacturer Information**

Brand	Panduit®
GTIN	00074983802340
Manufacturers Part Number	P10-14R-L
UPC	074983802340



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street  
72209-0000, AR Little Rock  
Phone: 501-565-1785  
Fax: 501-565-0827

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Ring Terminal

## Packaging

Carton ..... 50

Package ..... 500

Weight Per each ..... 0.26

## Uses, Certifications, and Standards

Enclosure ..... Ring shape

Mounting ..... 9/32

standard ..... UL Listed 587H E52164, CSA Certified LR31212

Temperature Rating ..... 302 Degrees Fahrenheit (150 Degrees Celsius)