

**BURNDY Catalog Number**  
**UPC Number**

**Description**  
**Status**

**Web Use**  
 BURNDY Product Line

K2A36U  
 7818106002077  
 TWO:2 STR-600 DUAL RTD,1/2 IN  
 Bolt Hole  
 Active

**Dimensional**

Width (in)	2.41
Length (in)	3.20
Bolt Hole Size (in)	0.50
Thickness	0.44
D - in	1.75
Pad Width (in)	2.42
N (in)	0.63

**General**

Number of Conductors	2
Number of Holes	1
Product Description	Aluminum Universal Terminal, 2 Conductor, 1 Hole, 2 AWG (Str)-600 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated

**Conductor(s)**

Aluminum Size (Range)	2 STR- 600 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-600 kcmil

**Physical**

Installation Torque	375
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	1/2
Plated (Yes or No)	N
Product Material	Aluminum

**Approvals / Certifications**

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

**Documentation**

For further technical assistance, please contact us


**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175



**BURNDY Catalog Number**  
**UPC Number**

K2A36U  
7818106002077  
TWO:2 STR-600 DUAL RTD,1/2 IN  
Bolt Hole  
Active

**Description**  
**Status**

**Web Use**  
BURNDY Product Line

**Dimensional**

Width (in)	2.41
Length (in)	3.20
Bolt Hole Size (in)	0.50
Thickness	0.44
D - in	1.75
Pad Width (in)	2.42
N (in)	0.63

**General**

Number of Conductors	2
Number of Holes	1
Product Description	Aluminum Universal Terminal, 2 Conductor, 1 Hole, 2 AWG (Str)-600 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated

**Conductor(s)**

Aluminum Size (Range)	2 STR- 600 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-600 kcmil

**Physical**

Installation Torque	375
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	1/2
Plated (Yes or No)	N
Product Material	Aluminum

**Approvals / Certifications**

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175