

Specifications



Eaton P48G11S15P

Eaton Mini-Power center, mini-power center, aluminum, NEMA 3R, 286, 60 Hz, single-phase, 480 V, 120/240 V, 2 at -5% FCBN, 115 °C rise, 15 KVA, indoor-outdoor, 107A15K

General specifications

PRODUCT NAME	Eaton Mini-Power center
CATALOG NUMBER	P48G11S15P
UPC	786680140228
PRODUCT LENGTH/DEPTH	11.6 in
PRODUCT HEIGHT	37.5 in
PRODUCT WIDTH	13.1 in
PRODUCT WEIGHT	232 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	ANSI IEEE Certified UL Listed CSA Certified

Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	286
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	107A15K

Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

Performance Ratings

FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	15 kVA

Resources

CATALOGS	Commercial Distribution Transformers, Volume 2, Tab 2
MULTIMEDIA	Eaton's Transformer Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - P48G11S15P

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

