



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LAM2A250386Y 2BRL Alcu Lug *Panduit Corporation*

|                  |  |
|------------------|--|
| Catalog Number   | LAM2A250386Y   |
| Manufacturer     | Panduit Corporation  |
| Description      | Two Barrel Lug, #6 Awg Conductor Size, 250 Kcmil Conductor Size, Non-Insulated, Copper Conductor Material, +90 °C Operating Temperature, 2.56 In Overall Length, Screw Terminal, 600 V |
| Weight per unit  | 1.3 (lbs/each)   |
| Product Category | Large Terminals & Connectors   |

### Features

|                 |          |
|-----------------|----------|
| amperage rating | NA       |
| Material        | Aluminum |
| media           | Yes      |
| Number of Holes | 1        |
| Stud Size       | 3/8      |
| Voltage Rating  | 600      |

### Material, Color, and Finish

|       |          |
|-------|----------|
| Color | Metallic |
|-------|----------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 2BRL ALCU LUG                       |
| extra long description | PAN LAM2A250-38-6Y Pan-Lug™ LAM2A25 |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | PANDUIT        |
| GTIN  | 00074983592555 |
| UPC   | 074983592555   |

### Taxonomies, Classifications, and Categories

|                      |                |
|----------------------|----------------|
| Category Description | SPLIT BOLTS    |
| Type                 | Mechanical Lug |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 12   |
| Weight Per each | 1.29 |

### Uses, Certifications, and Standards

|                   |  |
|-------------------|--|
| Application       | Stranded Aluminum or Copper Code Conductor                       |
| Mounting standard | 1<br>cULus Listed for use up to 600V & Temperature Rated to 90°C |