

Specifications

Photo is representative

Eaton PDG23F0030TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 30A, 25kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG2X3T100)



General specifications

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23F0030TFFJ
MODEL CODE	PDG23F0030TFFJ
UPC	786679281697
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	104.6 mm
PRODUCT WEIGHT	1.82 kg
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked IEC 60947-2 UL 489 CSA

Product specifications

AMPERAGE RATING	30 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	2
CLASS	Class A
INTERRUPT RATING	25 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	18 kAIC Icu/ 15/13 kAIC Ics/ 37.8 kAIC Icm @525V South Africa (IEC) 14 kAIC @600V (UL/CSA) 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @440V (IEC) 25 kAIC @480V (UL) 10 kAIC Icu @ 125 Vdc 20 kAIC Icu/ 20 kAIC Ics/ 42 kAIC Icm @480V Brazil (IEC) 35 kAIC @240V (UL) 10 kAIC Icu @250 Vdc 25 kAIC Icu/ 25 kAIC Ics/ 52.5 kAIC Icm @380-415V (IEC) 35 kAIC Icu/ 35 kAIC Ics/ 73.5 kAIC Icm

Resou
3D CAD DRAWING PACKAGE
APPLIC NOTES
BROCH
CATALO
CERTIF REPORT
INSTAL INSTRU

Specifications

Photo is representative

Eaton

PDG23F0030TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 30A, 25kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG2X3T100)



General specifications

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23F0030TFFJ
MODEL CODE	PDG23F0030TFFJ
UPC	786679281697
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	104.6 mm
PRODUCT WEIGHT	1.82 kg
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked IEC 60947-2 UL 489 CSA

Product specifications

AMPERAGE RATING	30 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	2
CLASS	Class A
INTERRUPT RATING	25 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	18 kAIC Icu/ 15/13 kAIC Ics/ 37.8 kAIC Icm @525V South Africa (IEC) 14 kAIC @600V (UL/CSA) 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @440V (IEC) 25 kAIC @480V (UL) 10 kAIC Icu @ 125 Vdc 20 kAIC Icu/ 20 kAIC Ics/ 42 kAIC Icm @480V Brazil (IEC) 35 kAIC @240V (UL) 10 kAIC Icu @250 Vdc 25 kAIC Icu/ 25 kAIC Ics/ 52.5 kAIC Icm @380-415V (IEC) 35 kAIC Icu/ 35 kAIC Ics/ 73.5 kAIC Icm

Resou
3D CAD DRAWING PACKAGE
APPLIC NOTES
BROCH
CATALO
CERTIF REPORT
INSTAL INSTRU