



LCAX614L 1-HL STD Flex Lug

Panduit Corporation

Catalog Number	LCAX614L
Manufacturer	Panduit Corporation
Description	The LCAX6-14-L Tin-Plated Copper Compression Lug, One-Hole, Standard Barrel, Has Color-Coded Barrels Marked With Panduit and Specified Competitor Die Index Numbers For Proper Crimp Die Selection. An Inspection Window Aids to Visually Assure Full Conductor Insertion, and The Tin-Plate Material Helps to Inhibit Corrosion. UL Listed and CSA Certified to 35 KV and Temperature Rated to 90°C.
Weight per unit	0.0178 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Tin-Plated Copper
media	Yes
Number of Holes	1
Stud Size	1/4

Material, Color, and Finish

Color	Blue
-------	------

Dimensions and Weight

Size	#6 AWG Class B, C, G, H, I, K, M and DLO
------	--

Descriptions

Description	1-HL STD FLEX LUG
extra long description	PAN LCAX6-14-L Pan-Lug™ LCAX6-14-L
Long Description	The LCAX6-14-L Tin-Plated Copper Compression Lug, one-hole, standard barrel, has color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection. An inspection window aids to visually assure full conductor insertion, and the tin-plate material helps to inhibit corrosion. UL Listed and CSA Certified to 35 KV and temperature rated to 90°C.
Product Type	Pan-Lug™ LCAX6-14-L Comp. Lug, 6, Flex, Tin PLT Copper, One
Special Features	Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2301 East Saint Elmo Rd. Suite 105
78744-0000, TX Austin
Phone: 512-443-5600
Fax: 512-443-5601

Manufacturer Information

Brand	PANDUIT
GTIN	00074983433582
Manufacturers Part Number	LCAX614L
UPC	074983433582

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Compression Lug

Packaging

Carton	1
Package	50
Weight Per each	0.0178

Uses, Certifications, and Standards

Mounting standard	9/16 C22.2 No. 65-13, 486A-486B File #E52164, ABS approved
-------------------	---