



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH500PG 500 Va Mte CTRL XFRMR 120X240V-12X24V *Hammond Power Solutions*

Catalog Number	PH500PG
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 120X240 PV, 12X24 SV, 500 Kva
Weight per unit	N/A
Product Category	Encapsulated Industrial Contro

Features

connection	Terminal Block
Input Voltage	120X240, 115x230, 110x220
Output Voltage	12X24, 11.5x23, 11x22
Phase	1 PH
Wattage	500 W

Dimensions and Weight

Height	AML21BBA2BA-007
Length	4.75 in.
Width	5.94 in

Descriptions

Description	500 VA MTE CTRL XFRMR 120X240V-12X24V
extra long description	HMND PH500PG CNTL 500VA 120X240-12X
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 120x240 PV, 12x24 SV, 500 kVA
Product Type	CNTL 500VA 120X240-12X24
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

Manufacturer Information

Brand	Hammond Power Solutions
Manufacturers Part Number	PH500PG
sub brand	Machine Tool Industrial Control Transformer

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	0



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Frequency Rating	50/60 Hz
Mounting standard	PANEL
Temperature Rating	CSA, UL, CE
	Typical 30 Average/ 40 Maximum