



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NCG5050 1/2" NM Cord Grip

*Crouse-Hinds*

Catalog Number	NCG5050
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series NCG Cord Grip, Cable Range Min/Max: 0.20-0.50", Non-Armoured and Tray Cable, Non-Armoured Gland, Polyamide 6, General Purpose, 1/2" NPT
Weight per unit	0.0300 (lbs/each)
Product Category	Cable & Cord Grips

### Features

dimensions	0.5000 IN X 0.5000 IN X 2.3800 IN
------------	-----------------------------------

### Descriptions

Description	1/2" NM CORD GRIP
extra long description	MIDWEST NCG50 50 1/2 NON METALLIC C
Features	For use with portable cord, Crouse-Hinds series NCG and NCGB watertight cord grips terminate and protect conductors from mechanical damage due to vibration and movement. A neoprene bushing seals out oils, coolants, water, dust and other abusive agents. NCG and NCGB cord grips may be used with types S, SO, STO, SJ, SJT, SJTO and SVO portable cords. NCGS non-metallic cord grips are used in both commercial and residential grid-tied PV solar applications and are designed to accommodate the entry of multiple
Long Description	Eaton Crouse-Hinds series NCG cord grip, Cable range min/max: 0.20-0.50", Non-armoured and tray cable, Non-armoured gland, Polyamide 6, General purpose, 1/2" NPT
Product Type	1/2 Non Metallic Cord Grip

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564002440
Manufacturers Part Number	NCG50 50
UPC	784564002440

### Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cord grip

### Packaging

Carton	1
Package	25
Weight Per each	0.03



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	NEMA 3 cULus Listed - UL File E23223
Temperature Rating	-25° to 40°C