



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NTCC150 1-1/2" Rigid Threadless Raintight Coupling *Appleton/Oz Gedney*

Catalog Number	NTCC150
Manufacturer	Appleton/Oz Gedney
Description	Coupling, Trade Size: 1-1/2 In, Outside Diameter: 2.69 In, Length: 3.31 In, Flexibility: Rigid and Imc, Material: Malleable Iron, Connection: Compression, Standard: UI 514B, UI File Number E11853, Nema FB-1, For Joining Lengths Of Steel Emt to Rigid Metal Conduit or Imc
Weight per unit	1.2 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Compression
outside diameter	2.6900000000000000;68.3260

### Dimensions and Weight

Length	3.3100000000000000;84.0740
--------	----------------------------

### Descriptions

Description	1-1/2" RIGID THREADLESS RAIN TIGHT COUPLING
extra long description	APP NTCC-150 1-1/2 IN CPLG NO THRD
Long Description	Coupling, Trade Size: 1-1/2 IN, Outside Diameter: 2.69 IN, Length: 3.31 IN, Flexibility: Rigid And IMC, Material: Malleable Iron, Connection: Compression, Standard: UL 514B, UL File Number E11853, NEMA FB-1, For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
Product Type	1-1/2 In CPLG No THRD RGD Cond
Special Features	Threadless, Concretetight

### Manufacturer Information

Brand	Appleton
GTIN	00781381638401
Manufacturers Part Number	NTCC-150
UPC	781381638401

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	COUPLING

### Trade Size

Trade Size	1-1/2
------------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	5
Package	25
Weight Per each	1.18

## Uses, Certifications, and Standards

Application	For Joining Lengths Of Steel EMT To Rigid Metal Conduit Or IMC
standard	UL 514B, UL File Number E11853, NEMA FB-1