





P2230

Wt/100 pcs: 310 Lbs (140.6 kg)




P2245

Wt/100 pcs: 315 Lbs (142.9 kg)




P2348

Wt/100 pcs: 274 Lbs (124.3 kg)




P1887

Wt/100 pcs: 297 Lbs (134.8 kg)




P2453

Wt/100 pcs: 116 Lbs (52.6 kg)



P2941, P2942

Wt/100 pcs: 358 Lbs (162.4 kg)



Standard Dimensions for 1 5/8" (41 mm) width series channel fittings (Unless Otherwise Shown on Drawing)


Hole Diameter: 9/16" (14.3mm); **Hole Spacing - From End:** 13/16" (20.6 mm); **Hole Spacing - On Center:** 1 7/8" (47.6 mm); **Width:** 1 5/8"(41mm); **Thickness:** 1/4" (6.4mm)

1 5/8" Channel
 Telestrut System
 Nuts & Hardware
 General Fittings
 Pipe/Conduit Supports
 Electrical Fittings
 Concrete Inserts
 1 1/4" Framing System
 1 3/16" Framing System
 Fiberglass System
 Special Metals
 PrimeAngle System
 Product Index



UNISTRUT®

GENERAL FITTINGS



- Flat Plate Fittings 90
- Ninety Degree Fittings 94
- Angular Fittings 101
- "Z" Shape Fittings 102
- "U" Shape Fittings 104
- Wing Shape Fittings 109
- Post Bases 112
- Brackets 114
- Brace Fittings 120
- Beam Clamps 122
- Trolleys 133
- Special Application Fittings 135

MATERIAL

Fittings, unless noted, are made from hot-rolled, pickled and oiled steel plates, strip or coil, and conform to ASTM specifications A575, A576, A635, or A36. The fitting steel also meets the physical requirements of ASTM A1011 SS GR 33. The pickling of the steel produces a smooth surface free from scale.

Many fittings are also available in stainless steel, aluminum and fiberglass. Consult factory for ordering information.

FINISHES

Fittings are available in: Perma-Green II (GR), electro-galvanized (EG), conforming to ASTM B633 Type III SC1; Hot-dipped galvanized (HG), conforming to ASTM A123 or A153 and plain (PL).

APPLICATION

All parts drawings illustrate only one application of each fitting. In most cases many other applications are possible. The channels shown in the illustrations are P1000, 1 5/8" square, except where noted otherwise.

All 5/16" diameter holes use 1/2" x 15/16" hex head cap screws and 1/2" nuts - P1010, P4010 or P5510 - depending on the channel used. Nuts and bolts are not included with the fitting and must be ordered separately.

DESIGN BOLT TORQUE

| BOLT SIZE | 1/4" | 5/16" | 3/8" | 1/2" | 5/8" | 3/4" |
|-----------|------|-------|------|------|------|------|
| FOOT LBS. | 6 | 11 | 19 | 50 | 100 | 125 |
| N·m | 8 | 15 | 25 | 70 | 135 | 170 |

DIMENSIONS

Imperial dimensions are illustrated in inches. Metric dimensions are shown in parenthesis or as noted. Unless noted, all metric dimensions are in millimeters and rounded to one decimal place.


DESIGN LOAD

Design load data, where shown, is based on the ultimate strength of the connection with a safety factor of 2.5, unless otherwise noted.




P2230

Wt/100 pcs: 310 Lbs (140.6 kg)




P2245

Wt/100 pcs: 315 Lbs (142.9 kg)




P2348

Wt/100 pcs: 274 Lbs (124.3 kg)




P1887

Wt/100 pcs: 297 Lbs (134.8 kg)




P2453

Wt/100 pcs: 116 Lbs (52.6 kg)



P2941, P2942

Wt/100 pcs: 358 Lbs (162.4 kg)



Standard Dimensions for 1 5/8" (41 mm) width series channel fittings (Unless Otherwise Shown on Drawing)


Hole Diameter: 9/16" (14.3mm); **Hole Spacing - From End:** 1 3/16" (20.6 mm); **Hole Spacing - On Center:** 1 7/8" (47.6 mm); **Width:** 1 5/8"(41mm); **Thickness:** 1/4" (6.4mm)

1 5/8" Channel
Telestrut System
Nuts & Hardware
General Fittings
Pipe/Conduit Supports
Electrical Fittings
Concrete Inserts
1 1/4" Framing System
1 3/16" Framing System
Fiberglass System
Special Metals
PrimeAngle System
Product Index



UNISTRUT®

GENERAL FITTINGS



| | |
|------------------------------------|-----|
| Flat Plate Fittings | 90 |
| Ninety Degree Fittings | 94 |
| Angular Fittings | 101 |
| "Z" Shape Fittings | 102 |
| "U" Shape Fittings | 104 |
| Wing Shape Fittings | 109 |
| Post Bases | 112 |
| Brackets | 114 |
| Brace Fittings | 120 |
| Beam Clamps | 122 |
| Trolleys | 133 |
| Special Application Fittings | 135 |

MATERIAL

Fittings, unless noted, are made from hot-rolled, pickled and oiled steel plates, strip or coil, and conform to ASTM specifications A575, A576, A635, or A36. The fitting steel also meets the physical requirements of ASTM A1011 SS GR 33. The pickling of the steel produces a smooth surface free from scale.

Many fittings are also available in stainless steel, aluminum and fiberglass. Consult factory for ordering information.

FINISHES

Fittings are available in: Perma-Green II (GR), electro-galvanized (EG), conforming to ASTM B633 Type III SC1; Hot-dipped galvanized (HG), conforming to ASTM A123 or A153 and plain (PL).

APPLICATION

All parts drawings illustrate only one application of each fitting. In most cases many other applications are possible. The channels shown in the illustrations are P1000, 1 $\frac{5}{8}$ " square, except where noted otherwise.

All $\frac{3}{16}$ " diameter holes use $\frac{1}{2}$ " x $\frac{15}{16}$ " hex head cap screws and $\frac{1}{2}$ " nuts - P1010, P4010 or P5510 - depending on the channel used. Nuts and bolts are not included with the fitting and must be ordered separately.

DESIGN BOLT TORQUE

| BOLT SIZE | $\frac{1}{4}$ " | $\frac{5}{16}$ " | $\frac{3}{8}$ " | $\frac{1}{2}$ " | $\frac{5}{8}$ " | $\frac{3}{4}$ " |
|-----------|-----------------|------------------|-----------------|-----------------|-----------------|-----------------|
| FOOT LBS. | 6 | 11 | 19 | 50 | 100 | 125 |
| N·m | 8 | 15 | 25 | 70 | 135 | 170 |

DIMENSIONS

Imperial dimensions are illustrated in inches. Metric dimensions are shown in parenthesis or as noted. Unless noted, all metric dimensions are in millimeters and rounded to one decimal place.

DESIGN LOAD

Design load data, where shown, is based on the ultimate strength of the connection with a safety factor of 2.5, unless otherwise noted.