



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PRL2A3600X42C PRL2A Interior For TFL 480Y/277V 3PH 4W 600A 42 CK Eaton Corp

Catalog Number	PRL2A3600X42C
Manufacturer	Eaton Corp
Description	Eaton Pow-R-Stock PRL2A Panelboard, Interior, 480Y/277V, Three-Phase, 4W, 600A, Circuit, Copper Bus
Weight per unit	60.0 (lbs/each)
Product Category	20151030170353

Features

amperage rating	600A
media	Yes
Phase	Three-phase
Short Circuit Rating	35000

Descriptions

Also Known As...	breaker box Fuse box breaker panel panelboard electric panel panel panel board load center
Description	PRL2A INTERIOR FOR TFL 480Y/277V 3PH 4W 600A 42 CK
extra long description	ETN PRL2A3600X42C 480Y/277V, 3PH, 4
Features	Panelboards Pow-R-Stock Plus Program provide interiors; type 1 and 3R boxes; surface and flush trims; factory-assembled panelboards; main breaker kits; branch breakers; lug kits; service entrance kits; ground kits; and 200% neutral kits. In addition, the distributor stocking program can be used with various Eaton commercial distribution products and is designed to meet UL67 standards for use in data center, industrial, commercial and healthcare facilities.
Long Description	Eaton Pow-R-Stock PRL2A panelboard, Interior, 480Y/277V, Three-phase, 4W, 600A, circuit, Copper bus
Product Type	480Y/277V, 3PH, 4W, 600A, Circuit

Manufacturer Information

Brand	Eaton
GTIN	00786687010715
Manufacturers Part Number	PLR2A3600X42C
UPC	786687010715



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BOXES & INTERIORS
Type	PRL2A Panelboard

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	60

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMs
Operating Temperature	40Å°C