

Project:	
Fixture Type:	
Location:	
Contact:	

P8222 Series

LED Flush Mount • Wet Location



Specifications:

Description:

The P8222 delivers a solution for flush mount, for both residential and commercial markets. In addition, the P8222 is wet located and is a cost effective solution for fire rated application. The P8222 features a 120V alternating current source and eliminates the need for a traditional LED driver. This modular approach results in an encapsulated luminaire that unites performance, cost and saftey benefits.

Construction:

- $\boldsymbol{\cdot}$ Diffused polycarbonate lens controls direct glare from the LEDs
- · Simple snap in installation for J-Box
- $\boldsymbol{\cdot}$ Die-cast aluminum construction with a powder coat paint finish
- · Can be installed in a 4" J-Box
- Lumen output and distribution comparable to a 100W incandescent lamp
- Suitable for use in IC or NON-IC Applications with 25°C (77°F) continuous room side ambient temperature.

Performance:


Input Power	17W
Input Voltage	120V
Input Frequency	60Hz
Lumens	1032 (LM-79)
ССТ	3000K
CRI	90+
LPW	60
Life	42,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Min. Start Temp	-30° C
Max. Operating Temp	30° C
Warranty	5 yrs.
Labels	cCSAus classified for wet locations
	ENERGY STAR® qualified

P8222-28/30K9-AC1-L10

Images:



Dimensions:



Included Mounting Options:

J-Box Mount



J-Box Adaptei



Catalog number:

Base	Finish	Color Temp	Voltage	Lumen Package
P8222	28 - White	30K9 - 3000K	AC1 - 120V	L10 - 1032 Lumens
		90 CRI		



P8222 Series

LED Flush Mount • Wet Location



P8222-28/30K9-AC1-L10

ELECTRICAL DATA P8222-28/30K9-AC1-L10

 Input Voltage
 120V

 Input Frequency
 60 Hz

 Constant Current Output
 700mA

 Power Factor
 ≥0.90

 THD
 <20%</td>

 EMI Filtering
 FCC 47CFR

 Part 15, Class B

Operating

Photometrics:

Temperature -30°C to 30°C

Dimming Yes*

Over-voltage, over-current, short-circuit protected *See Dimming Notes for more information


PERFORMANCE DATACHART

Single U	Single Unit, Initial Footcandles, 30" Work Plane				Single Unit, Initial Footcandles, 30" Work Plane Ceiling to Floor Multiple Units, Initial Footcandles, 30" Work Plane						ork Plane
Nadir		10°	20°			30°	Height (ft)	Spacing is Maximur	n Over Wo	rk Plane, S	SMH= 1.2
FC	FC	Dia (ft)	FC	Dia (ft)	FC	Dia (ft)		Fixture Spacing (ft)	RCR 2	RCR 5	RCR 7
32	30	1	24	3	17	4	6	4.0	53	37	30
13	12	2	10	4	7	6	8	7.0	21	15	12
6	6	3	5	6	3	9	10.5	10.0	10	7	6
4	4	3	3	7	2	11	12	11.0	7	5	4

P8222-28/30K9-AC1-L10

LED Light Engine: 3000K, 90 CRI System Wattage: 16.4 Fixture delivered lumens: 1032 Fixture Efficacy: 63.0

Fixture Etticacy: 63.0 Spacing Criteria: 1.2



CANDELA DISTRIBUTION

CANDEL
392
390
372
33 <i>7</i>
290
234
1 <i>75</i>
11 <i>7</i>
66
28
16

Test No. 14.00618 2768255-4

Tested at 25° Ambient in accordance to IESNA LM-79-2008

ZONAL LUMEN SUMMARY							
ZONE	LUMENS	%LUMINAIRE					
0-30	297	28.8					
0-40	478	46.3					
0-60	814	78.9					
0-90	1032	100.0					

COEFFICIENTS OF UTILIZATION

7onal Cavity Method

ZON		avity	/ /vie	moa	1					
		% Effective Ceiling Cavity Reflectance								
.≧	80%				70 %		50%		30%	
اءِ ق		20% Effective Floor Cavity Reflectance								
Room Cavity Ratio	% Wall Reflectance									
&	70	50	30	10	70	10	50	30	50	30
1	108	104	99	95	106	94	97	94	93	90
3	90	80	71	65	88	64	75	69	72	67
5	76	63	54	48	74	47	60	53	58	52
7	65	52	43	37	64	37	50	42	48	41
9	57	44	35	30	56	30	42	35	41	34
P8027-28/30K9-AC1-L10 Test No. 14.00618 2768255					3255					



P8222 Series

LED Flush Mount • Wet Location



Dimming Notes:

P8222-28/30K9-AC1-L10

P8222 is designed to be compatible with many Electronic Low Voltage (ELV-Reverse Phase) controls. LED rated dimmer controls may offer favorable dimming performance. The following is a partial list of known compatible dimmer controls:

Electronic Low Voltage ELV Reverse Phase Controls

Leviton	Renoir II	AWRMG-EAW
Lutron	Diva Series	(Part Number DVELV-300)
Lutron	Maestro Series	(Part Number MAELV-600)
Lutron	Nova T Series	(Part Number NTELV-300)
Lutron	Spacer Series	(Part Number SPSELV-600)
Lutron	Vierti Series	(Part Number VTELV-600)

LED Rated Controls

Pass & Seymour	(Part Number DCL453PTCCCV6)
,	,

Incandescent Digital type dimmers are not recommended.

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.