

# Eaton PSG480F24RM

Catalog Number: PSG480F24RM

Eaton PSG power supply, Aluminum, 400-500 Vac, 47-63 Hz, Finger-safe terminals, 24 Vdc output, Three-phase, 480W output power, -25°C-80°C operating temp



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton PSG general purpose power supply	PSG480F24RM
	UPC
	786685683607

<b>Product Length/Depth</b>	<b>Product Height</b>
7 in	7 in

<b>Product Width</b>	<b>Product Weight</b>
6 in	3.9 lb

<b>Warranty</b>	<b>Compliances</b>
3 year	RoHS Compliant
	CE Marked

**Certifications**

- UL 508
- EN Listed
- CSA Std. C22.2
- IEC Rated

## Product specifications

### Operating temperature - max

80 °C

### Operating temperature - min

-25 °C

### Phase

Three-phase

### Frequency rating

47-63 Hz

### Enclosure color

Aluminum

### Output voltage

24 V

### Terminals

Finger-safe

### Input voltage

400-500 Vac

### Output

480 W

## Resources

### Brochures

[Eaton's PSG Series Power Supplies](#)

### Installation instructions

[Installation Instructions for PSG480F Power Supply](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - PSG480F24RM](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton PSG480F24RM

Catalog Number: PSG480F24RM

Eaton PSG power supply, Aluminum, 400-500 Vac, 47-63 Hz, Finger-safe terminals, 24 Vdc output, Three-phase, 480W output power, -25°C-80°C operating temp



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton PSG general purpose power supply	PSG480F24RM
	UPC
	786685683607

<b>Product Length/Depth</b>	<b>Product Height</b>
7 in	7 in

<b>Product Width</b>	<b>Product Weight</b>
6 in	3.9 lb

<b>Warranty</b>	<b>Compliances</b>
3 year	RoHS Compliant
	CE Marked

**Certifications**

- UL 508
- EN Listed
- CSA Std. C22.2
- IEC Rated

## Product specifications

### Operating temperature - max

80 °C

### Operating temperature - min

-25 °C

### Phase

Three-phase

### Frequency rating

47-63 Hz

### Enclosure color

Aluminum

### Output voltage

24 V

### Terminals

Finger-safe

### Input voltage

400-500 Vac

### Output

480 W

## Resources

### Brochures

[Eaton's PSG Series Power Supplies](#)

### Installation instructions

[Installation Instructions for PSG480F Power Supply](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - PSG480F24RM](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)