

Eaton PSG60E24RM

Catalog Number: PSG60E24RM

Eaton PSG general purpose power supply, 60W, Single-phase, 24 Vdc output voltage, Metal enclosure, Removable terminals

General specifications



Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG60E24RM

UPC
786685520971

Product Length/Depth	Product Height
6.2 in	2.1 in

Product Width	Product Weight
6.5 in	0.37 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	German Safety RoHS Compliant

Certifications
CSA Certified
EN Listed
cUL Certified
IEC Rated
UL 508
cULus/UL 60950-1

Product specifications

Special features

Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection

Operating temperature - max

75 °C

Operating temperature - min

-20 °C

Power consumption

60 W

Phase

Single-phase

Enclosure material

Metal

Output voltage

24 V

Terminals

Removable

Series

PSG

Resources

Brochures

[Eaton's PSG Series Power Supplies](#)

Installation instructions

[Installation Instructions for PSG60E Power Supply](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - PSG60E24RM](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton PSG60E24RM

Catalog Number: PSG60E24RM

Eaton PSG general purpose power supply, 60W, Single-phase, 24 Vdc output voltage, Metal enclosure, Removable terminals

General specifications



Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG60E24RM

UPC
786685520971

Product Length/Depth	Product Height
6.2 in	2.1 in

Product Width	Product Weight
6.5 in	0.37 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	German Safety RoHS Compliant

Certifications
CSA Certified
EN Listed
cUL Certified
IEC Rated
UL 508
cULus/UL 60950-1

Product specifications

Special features

Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection

Operating temperature - max

75 °C

Operating temperature - min

-20 °C

Power consumption

60 W

Phase

Single-phase

Enclosure material

Metal

Output voltage

24 V

Terminals

Removable

Series

PSG

Resources

Brochures

[Eaton's PSG Series Power Supplies](#)

Installation instructions

[Installation Instructions for PSG60E Power Supply](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - PSG60E24RM](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)