



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RB300250 3" X 2-1/2" Reducing Bushing

Appleton/Oz Gedney

Catalog Number	RB300250
Manufacturer	Appleton/Oz Gedney
Description	Reducing Bushing, Size: 3 X 2-1/2 In, Material: Steel, Finish: Zinc Electroplate, Connection: NPT, Standard: Class I: Groups A, B, C, D, Class Ii: Groups E, F, G, Class Iii, UI 886 (1203), UI E10444, Csa C22.2 No. 25, C22.2 No. 30, Csa
Weight per unit	1.2 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	NPT
Material	Steel

### Material, Color, and Finish

Finish	Zinc Electroplate
--------	-------------------

### Dimensions and Weight

Size	3 X 2-1/2
------	-----------

### Descriptions

Description	3" X 2-1/2" REDUCING BUSHING
extra long description	APP RB300-250 RDC BUSH MALL 3TO2-1/
Long Description	Reducing Bushing, Size: 3 X 2-1/2 IN, Material: Steel, Finish: Zinc Electroplate, Connection: NPT, Standard: Class I: Groups A, B, C, D, Class II: Groups E, F, G, Class III, UL 886 (1203), UL E10444, CSA C22.2 No. 25, C22.2 No. 30, CSA
Product Type	RDC Bush Mall 3TO2-1/2 In NPT
Special Features	Smooth rounded integral bushing protects conductor insulation

### Manufacturer Information

Brand	Appleton
GTIN	00781381655552
Manufacturers Part Number	RB300-250
UPC	781381655552

### Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Reducing Bushing

### Packaging

Carton	25
Weight Per each	1.23



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Reducing Conduit Entries To A Smaller Size In Threaded Rigid  
And IMC Conduit Systems

standard

Class I: Groups A, B, C, D, Class II: Groups E, F, G, Class III, UL 886  
(1203), UL E10444, CSA C22.2 No. 25, C22.2 No. 30, CSA 065181