

Temporary power distribution

RhinoBox temporary power centers with GFCI protection E-series

Product description

50A input
20A, 30A, 50A output
120/240 V/AC (max.)



RB300ME

Features

- Safely centralize and distribute temporary power on the job site
- Unique patented “stackable” design allows multiple RhinoBox units to lock together for safe transport and storage
- NEMA Type 3R enclosures designed with two devices per circuit
- Available with manual or automatic GFCI reset configurations
- Weatherproof receptacle covers protect from damage and weather
- Flip-up circuit breaker cover prevent accidental tripping

RhinoBox E-series

| Rating A | V/AC | Distribution devices | Receptacle ratings | Protection | | Catalog no.* | |
|-------------|-----------------|---------------------------|-----------------------|------------|------|--------------|---|
| | | | | Overload | GFCI | | |
| 50 | 120/240 Max. | (6) WR duplex receptacles | 20A, 125V | ✓ | ✓ | □ RB300ME | • |
| | | (1) Locking receptacle | 30A, 250V | ✓ | — | | |
| | | (1) Locking inlet | 50A, 125/250V | — | — | | |
| | | (1) Locking outlet | 50A, 125/250V | — | — | | |
| 50 | 120/240 Max. | (6) WR duplex receptacles | 20A, 125V | ✓ | ✓ | □ RB300ME-L5 | • |
| | | (1) Locking receptacle | 30A, 125V | ✓ | — | | |
| | | (1) Locking inlet | 50A, 125/250V | — | — | | |
| | | (1) Locking outlet | 50A, 125/250V | — | — | | |
| 50 | 120/240 Max. | (6) Single receptacles | 20A, 125V | ✓ | ✓ | □ RB301ME | • |
| | | (1) Locking receptacle | 30A, 250V | ✓ | — | | |
| | | (1) Locking inlet | 50A, 125/250V | — | — | | |
| | | (1) Locking outlet | 50A, 125/250V | — | — | | |
| 50 | 120/240 Max. | (6) Locking receptacles | 20A, 125V | ✓ | ✓ | □ RB302ME | • |
| | | (1) Locking receptacle | 30A, 250V | ✓ | — | | |
| | | (1) Locking inlet | 50A, 125/250V | — | — | | |
| | | (1) Locking outlet | 50A, 125/250V | — | — | | |

*Automatic GFCI reset configurations are available. When ordering automatic RhinoBox replace “M” in Catalog no. with “A”.
Example: RB300AE = Automatic; RB300ME = Manual.



5-20R
L5-20R
L6-30R
Plug Non-NEMA 50A 125/250V CA Standard
Receptacle Non-NEMA 50A 125/250V CA Standard

Testing & code compliance: cETLus listed for outdoor use - NEMA Type 3R products. Complies with NEC® Articles 525 & 590 & OSHA Reg. 29CFR, Part 1926, Subpart K, 1926.404, GFCI requirements. Conforms to UL1640 and CSA C22.2, no. 14. **Material characteristics:** Enclosure: Cold-rolled 18 gauge steel. Legs: Cold-rolled 10 gauge steel.

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-32