



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave.
76067-0000, TX Mineral Wells
Phone: 940-325-5503
Fax: 940-325-5544



PSG240E24SMB Power Supply Heavy Duty Screw Terminals

Eaton Corp

Catalog Number	PSG240E24SMB
Manufacturer	Eaton Corp
Description	Power Supply, 240W, Single-Phase, 100-240V Input Voltage, 24 VDC Output Voltage, Metal Enclosure, Heavy-Duty Screw Terminals, Red Led
Weight per unit	0.6200 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions	7.5000 IN X 7.0000 IN X 1.7000 IN
media	Yes

Descriptions

Description	POWER SUPPLY HEAVY DUTY SCREW TERMINALS
extra long description	ETN PSG240E24SMB Power supply, Heav
Features	The PSG line of general purpose power supplies is used in a wide variety of industrial control applications. Applications include communication networks, sensors, PLCs and many other electrical systems. Each model is equipped with the options of a rugged metal or plastic housing, heavy-duty screw or finger-safe terminals and a variety of protection features. The PSG line offers the flexibility of operating with a universal input voltage of 100-240 Vac. It also provides system protection and continuous oper
Long Description	Power Supply, 240W, Single-phase, 100-240V input voltage, 24 Vdc output voltage, metal enclosure, Heavy-duty screw terminals, Red LED
Product Type	Power Supply, Heavy Duty Screw Terminals

Manufacturer Information

Brand	Eaton
GTIN	00786689791933
Manufacturers Part Number	PSG240E24SMB
UPC	786689791933

Taxonomies, Classifications, and Categories

Category Description	POWER SUPPLIES
Type	General purpose power supply

Packaging

Carton	1
Weight Per each	0.62



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 North East 20th Ave.
76067-0000, TX Mineral Wells
Phone: 940-325-5503
Fax: 940-325-5544

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - Other

standard

EN Listed,cULus/UL 60950-1,IEC Rated,cUL Recognized,German
Safety,RoHS Compliant,CE Marked