



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



REN40 40A 250V Superlag Renewable Fuse

Bussmann Fuses

Catalog Number	REN40
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Ren Fuse, Time Lag, Non Current-Limiting, Industrial and Commercial Structures, 40 A, Class H, Non-Indicating, 10 Kaic, Standard, 10, 250 V
Weight per unit	0.1300 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	40
class	Class H
dimensions	0.8200 IN X 0.8200 IN X 2.9800 IN
interrupt rating	10
Voltage Rating	250 V

Descriptions

Description	40A 250V SUPERLAG RENEWABLE FUSE
extra long description	BUSS REN-40 SUPER LAG RENEWABLE FUS
Features	Non-current limiting, renewable 250V (REN) and 600V (RES) Class H size fuses and fuse links (250V LKN and 600V LKS) for use in electrical systems where the available fault current is less than 10,000 amps and frequent outages dictate the economy of these renewable type fuses.
Long Description	Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 40 A, Class H, Non-indicating, 10 kAIC, Standard, 10, 250 V
Product Type	Super Lag Renewable Fuse 40/250
Special Features	Super lag, time lag, non current-limiting

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712100403
Manufacturers Part Number	REN-40
UPC	051712100403

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

Packaging

Carton	10
Weight Per each	0.13



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	Not Applicable