



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV1410RC 16-14 Vinyl Ins Ring Terminal Blue # 10 Stud *Panduit Corporation*

Catalog Number	PV1410RC
Manufacturer	Panduit Corporation
Description	The PV14-10R-C Pan-Term® Terminal Is A Vinyl Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.2900 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	#14

### Material, Color, and Finish

Color	Blue
Finish	Tin-Plated

### Dimensions and Weight

Size	#10
------	-----

### Descriptions

Description	16-14 VINYL INS RING TERMINAL BLUE # 10 STUD
extra long description	PAN PV14-10R-C Pan-Term® PV14-10R-C
Long Description	The PV14-10R-C Pan-Term® Terminal is a vinyl insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV14-10R-C Ring Terminal, Blue, Vinyl, 14-16 Awg,

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983801206
Manufacturers Part Number	PV14-10R-C
UPC	074983801206



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Ring Terminal

## Availability

minimum qty ..... 100

## Packaging

Carton ..... 100

Package ..... 500

Weight Per each ..... 0.29

## Uses, Certifications, and Standards

Enclosure ..... Ring shape

Mounting ..... 5/16

standard ..... cULus Listed 587H E52164, CSA Certified LR31212

Temperature Rating ..... 221 Degrees Fahrenheit (105 Degrees Celsius)