



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RHDH163PTC Radiant Dehum Fan Speed CTRL 1.6A, Tri

*Pass & Seymour/Legrand*

Catalog Number	RHDH163PTC
Manufacturer	Pass & Seymour/Legrand
Description	1.6A 120V Radiant Dehummer Fan Control, Tri-Color
Weight per unit	0.3000 (lbs/each)
Product Category	Fan Speed Switches & Controls

### Features

amperage rating	1.6
connection	Back Wired
Contact Rating	120VAC
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
Poles	Single Pole, 3-Way
Switch Type	Paddle
Voltage	120.0 V
Voltage Rating	120

### Material, Color, and Finish

Color	Ivory, Light Almond, White
-------	----------------------------

### Dimensions and Weight

Size	Depth 1.25" x Width 1.75" x Height 4.25"
------	--

### Descriptions

Description	RADIANT DEHUM FAN SPEED CTRL 1.6A, TRI
extra long description	P&S RHDH163PTC RADIANT DEHUM FAN SP
Features	Fan Control
Long Description	1.6A 120V Radiant DeHummer Fan Control, Tri-Color
Product Type	Radiant Dehum Fan Speed CTRL 1.6A, Tri
Special Features	This fan control offers a specially designed capacitive circuitry de-hummer feature that virtually eliminates fan motor ""hum"" for quiet fan speed control.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007053418
Manufacturers Part Number	RHDH163PTC
UPC	785007053418



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	radiant® Fan Speed Control

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	24
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Residential
Enclosure	Thermoplastic
environmental conditions	Indoor Only
Mounting	WALL
Operating Temperature	0°C to 40°C
standard	CULUS, UL, CSA Listed, cULus, UL Listed