



GE  
Lighting

43693 - Q150CL/DC

GE T4



**GENERAL CHARACTERISTICS**

Lamp Type	Halogen - Single-Ended
Bulb	T4
Base	Double Contact Bayonet (BA15d)
Filament	CC-8
Bulb Finish	Clear
Rated Life	2000.0 hrs

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	2800.0
Color Temperature	2950.0 K
Nominal Initial Lumens per Watt	18

**ELECTRICAL CHARACTERISTICS**


Wattage	150.0
Voltage	120.0

**DIMENSIONS**

Maximum Overall Length (MOL)	2.5000 in(63.5 mm)
Bulb Diameter (DIA)	0.500 in(12.7 mm)
Light Center Length (LCL)	1.375 in(34.9 mm)

**PRODUCT INFORMATION**

Product Code	43693
Description	Q150CL/DC
ANSI Code	ETC
Standard Package	Case
Standard Package GTIN	10043168436936
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168436939



**CAUTIONS & WARNINGS**

**Caution**

- Risk of Burn
  - Allow lamp to cool before handling.
  - Turn power off before installing lamp.
- Lamp may shatter and cause injury if broken
  - Dispose of lamp in a closed container.
  - Do not use lamp if outer glass is scratched or broken.

**Warning**

- Lamp emits UV radiation which may cause eye/skin irritation.
  - Avoid exposure of eyes and skin to unshielded lamp.
- Risk of Electric Shock
  - Turn power off before inspection, installation or removal.
- Risk of Fire
  - Keep combustible materials away from lamp.
  - Use in enclosed fixture rated for this product.
- Unexpected lamp rupture may cause injury, fire, or property damage
  - Use eye protection when handling lamp.
  - Use in enclosed fixture rated for this product.
  - Do not touch glass with bare hands.
  - Do not use lamp if outer glass is scratched or broken.
  - Do not exceed 110% of rated voltage.



GE  
Lighting

43693 - Q150CL/DC

GE T4



### GENERAL CHARACTERISTICS

Lamp Type	Halogen - Single-Ended
Bulb	T4
Base	Double Contact Bayonet (BA15d)
Filament	CC-8
Bulb Finish	Clear
Rated Life	2000.0 hrs

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens	2800.0
Color Temperature	2950.0 K
Nominal Initial Lumens per Watt	18

### ELECTRICAL CHARACTERISTICS


Wattage	150.0
Voltage	120.0

### DIMENSIONS

Maximum Overall Length (MOL)	2.5000 in(63.5 mm)
Bulb Diameter (DIA)	0.500 in(12.7 mm)
Light Center Length (LCL)	1.375 in(34.9 mm)

### PRODUCT INFORMATION

Product Code	43693
Description	Q150CL/DC
ANSI Code	ETC
Standard Package	Case
Standard Package GTIN	10043168436936
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168436939



### CAUTIONS & WARNINGS

#### Caution

- Risk of Burn
  - Allow lamp to cool before handling.
  - Turn power off before installing lamp.
- Lamp may shatter and cause injury if broken
  - Dispose of lamp in a closed container.
  - Do not use lamp if outer glass is scratched or broken.

#### Warning

- Lamp emits UV radiation which may cause eye/skin irritation.
  - Avoid exposure of eyes and skin to unshielded lamp.
- Risk of Electric Shock
  - Turn power off before inspection, installation or removal.
- Risk of Fire
  - Keep combustible materials away from lamp.
  - Use in enclosed fixture rated for this product.
- Unexpected lamp rupture may cause injury, fire, or property damage
  - Use eye protection when handling lamp.
  - Use in enclosed fixture rated for this product.
  - Do not touch glass with bare hands.
  - Do not use lamp if outer glass is scratched or broken.
  - Do not exceed 110% of rated voltage.