



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RACH24L125I CH Retrofit Kit Int Only 1 PH 125A Main Lug Only 2

Eaton Corp

Catalog Number	RACH24L125I
Manufacturer	Eaton Corp
Description	Eaton CH 3/4-Inch Loadcenter Retrofit Stocking Kit, Main Lug Only, 125 A, Size Group A, Cover Height: 33 In, Cover Width: 24 In, Nema 1, CH, Surface, Flush, 24 Circuits, Single-Phase, 0.75 In, #4-2/0 Awg
Weight per unit	13.2 (lbs/each)
Product Category	Load Center Accessories

Features

dimensions	6.0000 IN X 22.0000 IN X 30.0000 IN
------------	-------------------------------------

Descriptions

Description	CH RETROFIT KIT INT ONLY 1 PH 125A MAIN LUG ONLY 2
extra long description	ETN RACH24L125I Eaton CH retrofit k
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit,Main lug only,125 A,size group a,Cover height: 33 in,Cover width: 24 in,NEMA 1,CH,Surface,flush,24 Circuits,Single-phase,0.75 in,#4-2/0 AWG
Product Type	Eaton CH Retrofit Kit

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685211060
Manufacturers Part Number	RACH24L125I
UPC	786685211060

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Accessory

Packaging

Carton	1
Weight Per each	13.1999



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application
standard

Other
UL 67