



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD38TRLA Radiant SP/3WAY SW+15A TR Outlet La *Pass & Seymour/Legrand*

Catalog Number	RCD38TRLA
Manufacturer	Pass & Seymour/Legrand
Description	15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, Light Almond
Weight per unit	0.2080 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	125
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Poles	3-Way, Single Pole
Switch Type	Push
Voltage	125.0 V
Voltage Rating	125

Material, Color, and Finish

Color	Light Almond
-------	--------------

Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	------------------------------------------

Descriptions

Description	RADIANT SP/3WAY SW+15A TR OUTLET LA
extra long description	P&S RCD38TRLA RADIANT SP/3WAY SW+15
Features	Combination, Locator Light
Long Description	15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, Light Almond
Product Type	Radiant SP/3WAY SW+15A TR Outlet La
Special Features	The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007055061
Manufacturers Part Number	RCD38TRLA
UPC	785007055061

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Switch, Outlet

Packaging

Carton	1
Package	12
Weight Per each	0.208

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	CULUS, UL, cULus, UL Listed