



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S201UK15 MCB 1P K 15A 240 BCPD

*Industrial Connections &*

Catalog Number	S201UK15
Manufacturer	Industrial Connections &
Description	Miniature Circuit Breaker, Branch Circuit Protection, Rated Current 15 Amps, 1 Pole, Interrupt Rating 10 Ka, Thermal Magnetic Trip Curve K, Voltage Up to 240 Vac, Din Rail Mounted, Finger Safe and Multi-Function Terminals, UI 489, Csa 22.2 No. 5
Weight per unit	0.3050 (lbs/each)
Product Category	1 Pole Din Rail Mount Circuit

### Features

amperage rating	15 W
interrupt rating	10 kA
Poles	1 PH
Trip Type	OUTSIDE CORNER FITTING, OUTSIDE CORNER FITTING TYPE; ABS PLASTIC MATERIAL; 1.5 INCH L X 0.91 INCH W X 0.6 INCH H SIZE; WHITE FINISH; PAN-WAY LD10 SERIES NON-METALLIC SURFACE RACEWAY USED ON; UL, CE APPROVAL; 10 STANDARD PACKAGE; PAN-WAY[R] BRAND
Voltage Rating	240 W

### Dimensions and Weight

Height	92mm
Length	71 Millimeters
Width	17.5mm

### Descriptions

Description	MCB 1P K 15A 240 BCPD
extra long description	ABB S201U-K15 MCB 1P K 15A 240 BCPD
Long Description	Miniature Circuit Breaker, Branch Circuit Protection, Rated Current 15 Amps, 1 Pole, Interrupt Rating 10 kA, Thermal Magnetic Trip Curve K, Voltage up to 240 VAC, DIN Rail Mounted, Finger Safe and Multi-Function Terminals, UL 489, CSA 22.2 No. 5
Product Type	MCB 1P K 15A 240 BCPD
Special Features	DIN Rail Mounting, Finger Safe and Multi-Function Terminals

### Manufacturer Information

Brand	ABB
GTIN	00804325629263
Manufacturers Part Number	S201U-K15
UPC	804325629263



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	High Performance MCB, Branch Circuit Protection

## Packaging

Carton	1
Package	10
Weight Per each	0.305

## Uses, Certifications, and Standards

Application	For use as branch protection
Frequency Rating	50/60 Hz
Operating Temperature	-25 to +55 Degrees Celcius
standard	UL 489, CSA 22.2 No. 5, IEC 60947-2, UL E212323