



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RHCL453PTC Radiant CFL/Led SP/3W 450W Tri-Color

Pass & Seymour/Legrand

Catalog Number	RHCL453PTC
Manufacturer	Pass & Seymour/Legrand
Description	450W 120V Radiant CFL/Fed Single Pole/3-Way Dimmer, Tri-Color
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

Features

Connection Type	Screw Terminal
load	LED, Incandescent, CFL
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
Switch Type	Paddle
Voltage	120.0 V
Voltage Rating	120
Wattage	700

Material, Color, and Finish

Color	Ivory, Light Almond, White
-------	----------------------------

Descriptions

Description	RADIANT CFL/LED SP/3W 450W TRI-COLOR
extra long description	P&S RHCL453PTC RADIANT CFL/LED SP/3
Long Description	450W 120V Radiant CFL/FED Single Pole/3-Way Dimmer, Tri-Color
Product Type	Radiant CFL/Led SP/3W 450W, Tri-Color
Special Features	The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes. This dimmer is multi-location dimming with 3-Way wiring for simple installation.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007053487
Manufacturers Part Number	RHCL453PTC
UPC	785007053487

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 15.0

Packaging

Carton 1

Package 24

Weight Per each 0.25

Uses, Certifications, and Standards

Application Residential

Enclosure Thermoplastic

environmental conditions Humidity: Less than 95% non condensing

Mounting Box Mount

standard CULUS, UL, CSA Listed, cULus, UL Listed