



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29866 3.5W 50K Led BLNT Candelabra

Satco

| | |
|------------------|-------------------------------------|
| Catalog Number | S29866 |
| Manufacturer | Satco |
| Description | Satco S29866 4W CTC/Led/50K/CL/120V |
| Weight per unit | 0.0200 (lbs/each) |
| Product Category | Led Decorative C, Ca, F, G Sha |

Features

| | |
|----------------|----------------|
| average life | 15000 |
| connection | Candelabra |
| Fixture Type | LED Filament |
| lumens | 350 |
| Shape | C11 |
| Voltage Rating | 120 |
| Warranty | 3 Year Limited |
| Wattage | 4 |

Material, Color, and Finish

| | |
|-------|-----------|
| Color | Colorless |
|-------|-----------|

Dimensions and Weight

| | |
|------|----------------------|
| Size | MOL: 3.88, MOD: 1.38 |
|------|----------------------|

Descriptions

| | |
|------------------|---|
| Description | 3.5W 50K LED BLNT CANDELABRA |
| Long Description | SATCO S29866 4W CTC/LED/50K/CL/120V |
| Product Type | 4W CTC/Led/50K/CL/120V |
| Special Features | CEC: Non-Compliant - Not 82 CRI ; Dimmable: Yes Dimmable ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; 5000K color temperature ; 80 CRI ; 360 degree beam spread ; Enclosed lamp rated ; 3 Year Limited Warranty |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923298660 |
| Manufacturers Part Number | S29866 |
| sub brand | Satco |
| UPC | 045923298660 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type | LED |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status Inactive

Packaging

Carton 1

Weight Per each 0.02

Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)

standard cULus damp location rated