



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S10N06P01P 1KVA Buck Boost Transformer 1PH 120X240-16/32V

Eaton Corp

|                  |   |
|------------------|---|
| Catalog Number   | S10N06P01P  |
| Manufacturer     | Eaton Corp  |
| Description      | Eaton, General Purpose Encapsulated Transformer, Ep, Single-Phase, PV: 120 X 240V, Taps: None, SV: 16/32V, 115°C, 1 Kva, Al Windings, Frame: 67P, Indoor-Outdoor. |
| Weight per unit  | 1.0 (lbs/each)  |
| Product Category | Single Phase Non Ventilated to  |

### Features

|                   |                                    |
|-------------------|------------------------------------|
| connection        | 3C                                 |
| design            | EP                                 |
| dimensions        | 6.5600 IN X 5.5300 IN X 13.0300 IN |
| frame             | 67P                                |
| Number of Phases  | Single-phase                       |
| Primary Voltage   | 120 V, 240 V                       |
| Secondary Voltage | 16/32 V                            |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1KVA BUCK BOOST TRANSFORMER 1PH 120X240-16/32V  |
| extra long description | ETN S10N06P01P 1KVA BUCK BOOST XFMR   |
| Features               | Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA. |
| Long Description       | Eaton, general purpose encapsulated transformer, ep, single-phase, pv: 120 x 240v, taps: none, sv: 16/32v, 115°C, 1 kva, al windings, frame: 67p, indoor-outdoor.   |
| Product Type           | 1KVA Buck Boost XFMR 1PH 120X240-16/32V   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786680073601 |
| Manufacturers Part Number | S10N06P01P     |
| UPC                       | 786680073601   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

|                      |                           |
|----------------------|---------------------------|
| Category Description | BUCK & BOOST TRANSFORMERS |
| Type                 | Encapsulated transformer  |

## Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 1 |

## Uses, Certifications, and Standards

|                    |   |
|--------------------|---|
| Application        | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
| Frequency Rating   | 60 Hz   |
| standard           | UL Listed   |
| Temperature Rating | 115 °C rise   |