

SAFETY DATA SHEET

1. Identification

Product identifier	SC65 Putty Sealing Compound
Other means of identification	
SDS number	SDS-00034
Product code	SC65
Recommended use	Sealing Cables
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Company name	Thomas & Betts Corporation
Address	8155 T & B Boulevard Memphis, TN 38125 US
Telephone	901-252-5000 ext.8324
E-mail	Not available.
Emergency phone number	For Hazardous Materials [or Dangerous Goods] Incident Spill, Leak, Fire, Exposure, or Accident Call CHEMTREC Day or Night +1 703-741-5970

2. Hazard(s) identification

Physical hazards	Not classified.	
Health hazards	Skin corrosion/irritation	Category 2
	Serious eye damage/eye irritation	Category 1
	Sensitization, skin	Category 1
	Specific target organ toxicity, single exposure	Category 3 respiratory tract irritation
	Specific target organ toxicity, repeated exposure	Category 2
Environmental hazards	Hazardous to the aquatic environment, acute hazard	Category 2
	Hazardous to the aquatic environment, long-term hazard	Category 2
OSHA defined hazards	Not classified.	

Label elements



Signal word	Danger
Hazard statement	Causes skin irritation. May cause an allergic skin reaction. Causes serious eye damage. May cause respiratory irritation. May cause damage to organs through prolonged or repeated exposure. Toxic to aquatic life with long lasting effects.
Precautionary statement	
Prevention	Do not breathe mist or vapor. Wash thoroughly after handling. Use only outdoors or in a well-ventilated area. Contaminated work clothing must not be allowed out of the workplace. Avoid release to the environment. Wear eye protection/face protection. Wear protective gloves.
Response	If on skin: Wash with plenty of water. If inhaled: Remove person to fresh air and keep comfortable for breathing. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a poison center/doctor. Take off contaminated clothing and wash before reuse. If skin irritation or rash occurs: Get medical advice/attention. Collect spillage.
Storage	Store in a well-ventilated place. Keep container tightly closed. Store locked up.

Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	CAS number	%
Talc	14807-96-6	30 - 60
Epoxy Resin	Mixture	10 - 30
Quartz	14808-60-7	0.1 - 1

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention immediately.
Ingestion	Rinse mouth. Get medical attention if symptoms occur.
Most important symptoms/effects, acute and delayed	Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result. May cause respiratory irritation. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash. Prolonged exposure may cause chronic effects.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	If you feel unwell, seek medical advice (show the label where possible). Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

5. Fire-fighting measures

Suitable extinguishing media	Use fire-extinguishing media appropriate for surrounding materials.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire fighting equipment/instructions	Move containers from fire area if you can do so without risk.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Do not breathe mist or vapor. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
--	--

Methods and materials for containment and cleaning up

Prevent product from entering drains.

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS. Use a vacuum cleaner. If not possible collect using a shovel, broom or the like.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage**Precautions for safe handling**

Do not breathe mist or vapor. Do not get this material in contact with eyes. Avoid contact with eyes, skin, and clothing. Provide adequate ventilation. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices.

Conditions for safe storage, including any incompatibilities

Store locked up. Store in original tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-3 (29 CFR 1910.1000)**

Components	Type	Value	Form
Quartz (CAS 14808-60-7)	TWA	0.3 mg/m3	Total dust.
		0.1 mg/m3	Respirable.
		2.4 mppcf	Respirable.
Talc (CAS 14807-96-6)	TWA	0.3 mg/m3	Total dust.
		0.1 mg/m3	Respirable.
		20 mppcf	Respirable.
2.4 mppcf			

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Quartz (CAS 14808-60-7)	TWA	0.025 mg/m3	Respirable fraction.
Talc (CAS 14807-96-6)	TWA	2 mg/m3	Respirable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
Quartz (CAS 14808-60-7)	TWA	0.05 mg/m3	Respirable dust.
Talc (CAS 14807-96-6)	TWA	2 mg/m3	Respirable.

Biological limit values

No biological exposure limits noted for the ingredient(s).

Exposure guidelines

Occupational Exposure Limits are not relevant to the current physical form of the product.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower must be available when handling this product.

Individual protection measures, such as personal protective equipment**Eye/face protection**

Chemical respirator with organic vapor cartridge and full facepiece.

Skin protection**Hand protection**

Wear appropriate chemical resistant gloves. Suitable gloves can be recommended by the glove supplier.

Skin protection**Other**

Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.

Respiratory protection

When engineering controls are not sufficient to lower exposure levels below the applicable exposure limit, use a NIOSH approved respirator.

Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

9. Physical and chemical properties

Appearance	Paste.
Physical state	Liquid.
Form	Liquid. Paste.
Color	Blue. Gray.
Odor	Mild.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	205 °C (401°F)
Evaporation rate	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	1.05
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Explosive properties	Not explosive.
Oxidizing properties	Not oxidizing.
Percent volatile	0.0 % (calculated)

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Heat, flames and sparks. Protect against direct sunlight. Contact with incompatible materials.
Incompatible materials	Oxidizing agents. Acids. Bases. Amines.
Hazardous decomposition products	Carbon oxides. Nitrogen oxides (NOx). Aldehydes. Acids. Phenol. Toxic fumes. Irritating vapors

11. Toxicological information

Information on likely routes of exposure

Inhalation	May cause damage to organs through prolonged or repeated exposure by inhalation. May cause irritation to the respiratory system.
Skin contact	Causes skin irritation. May cause an allergic skin reaction.
Eye contact	Causes serious eye damage.
Ingestion	Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics	Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result. May cause respiratory irritation. Skin irritation. May cause redness and pain. May cause an allergic skin reaction. Dermatitis. Rash.
---	--

Information on toxicological effects

Acute toxicity	Low hazard.
-----------------------	-------------

Components	Species	Test Results
Talc (CAS 14807-96-6)		
Acute		
<i>Oral</i>		
LD50	Rat	> 5000 mg/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Causes skin irritation.
----------------------------------	-------------------------

Serious eye damage/eye irritation	Causes serious eye damage.
--	----------------------------

Respiratory or skin sensitization

Respiratory sensitization	Not a respiratory sensitizer.
----------------------------------	-------------------------------

Skin sensitization	May cause an allergic skin reaction.
---------------------------	--------------------------------------

Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
-------------------------------	--

Carcinogenicity	Due to the form of the product, exposure to the potentially carcinogenic components is not expected.
------------------------	--

IARC Monographs. Overall Evaluation of Carcinogenicity

Quartz (CAS 14808-60-7)

1 Carcinogenic to humans.

Talc (CAS 14807-96-6)

3 Not classifiable as to carcinogenicity to humans.

NTP Report on Carcinogens

Quartz (CAS 14808-60-7)

Known To Be Human Carcinogen.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
------------------------------	--

Specific target organ toxicity - single exposure	May cause respiratory irritation.
---	-----------------------------------

Specific target organ toxicity - repeated exposure	May cause damage to organs through prolonged or repeated exposure.
---	--

Aspiration hazard	Not an aspiration hazard.
--------------------------	---------------------------

Chronic effects	May cause damage to organs through prolonged or repeated exposure. Prolonged exposure may cause chronic effects.
------------------------	--

12. Ecological information

Ecotoxicity	Toxic to aquatic life with long lasting effects.
--------------------	--

Persistence and degradability	No data is available on the degradability of this product.
--------------------------------------	--

Bioaccumulative potential	No data available.
----------------------------------	--------------------

Mobility in soil	This substance has low mobility in the environment.
-------------------------	---

Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.
------------------------------	---

13. Disposal considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT

UN number	UN3082
UN proper shipping name	Environmentally hazardous substances, liquid, n.o.s. (Epoxy Resin)
Transport hazard class(es)	
Class	9
Subsidiary risk	-
Label(s)	9
Packing group	III
Environmental hazards	
Marine pollutant	Yes
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	8, 146, 335, IB3, T4, TP1, TP29
Packaging exceptions	155
Packaging non bulk	203
Packaging bulk	241

IATA

UN number	UN3082
UN proper shipping name	Environmentally hazardous substance, liquid, n.o.s. (Epoxy Resin)
Transport hazard class(es)	
Class	9
Subsidiary risk	-
Packing group	III
Environmental hazards	Yes
ERG Code	9L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

IMDG

UN number	UN3082
UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Epoxy Resin)
Transport hazard class(es)	
Class	9
Subsidiary risk	-
Packing group	III
Environmental hazards	
Marine pollutant	Yes
EmS	F-A, S-F
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not established.

15. Regulatory information

US federal regulations	This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200. All components are on the U.S. EPA TSCA Inventory List.
-------------------------------	---

Country(s) or region	Inventory name	On inventory (yes/no)*
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s).

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 17-December-2015

Revision date 11-May-2016

Revision # 2

HMIS® ratings Health: 3*
Flammability: 1
Physical hazard: 0

NFPA ratings



Disclaimer

Thomas & Betts Corporation cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.