



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 South Persimmon Street
77375-6855, TX Tomball
Phone: 281-357-5300
Fax: 281-357-5005



SC850S10C0 7.87" 50LB BLK CBL Tie *Panduit Corporation*

Catalog Number	SC850S10C0
Manufacturer	Panduit Corporation
Description	The SC8-50-S10-C0 Stronghold Clamp Cable Ties Offers Contractors An Economical Clamp Cable Tie Option For Commercial Construction and General-Purpose Applications. The Cable Tie Design Allows You to Secure Cable Bundles to Another Surface, For Use With #10 (M5) Screw. Standard, 7.87" (200MM) Length and Are For Outdoor Use. Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 50.
Weight per unit	0.3670 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	7.9
Thickness	0.06
Width	NA

Descriptions

Description	7.87" 50LB BLK CBL TIE
extra long description	PAN SC8-50-S10-C0 StrongHold™ SC8-5
Long Description	The SC8-50-S10-C0 StrongHold Clamp Cable Ties offers contractors an economical clamp cable tie option for commercial construction and general-purpose applications. The cable tie design allows you to secure cable bundles to another surface, for use with #10 (M5) screw. Standard, 7.87" (200mm) length and are for outdoor use. Made of Weather Resistant Nylon 6.6, are black in color and come in packages of 50.
Product Type	Stronghold™ SC8-50-S10-C0 Cable Tie, Black, Pa 6.6, 50LB Min
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	Panduit®
GTIN	00613056258334
Manufacturers Part Number	SC8-50-S10-C0
UPC	613056258334

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 South Persimmon Street
77375-6855, TX Tomball
Phone: 281-357-5300
Fax: 281-357-5005

Availability

minimum qty 100

Packaging

Carton 100

Package 1000

Weight Per each 0.367

Uses, Certifications, and Standards

standard UL 62275 Compliant (Type 1, 11), UL Recognized #E56854, RoHS
Compliant