



T58 1-1/2" Cond Body

Appleton/Oz Gedney

Catalog Number	T58
Manufacturer	Appleton/Oz Gedney
Description	FM8 Grayloy-Iron Unilets Type T Conduit Outlet Body, Hub Size: 1-1/2 In, Form: 8, Length: 10.38 In, Width: 4.03 In, Height: 2.78 In, Material: Grayloy-Iron, Finish: Triple-Coat (Zinc Electroplate, Chromate and Epoxy Powder Coat), Color: Gray,
Weight per unit	5.7 (lbs/each)
Product Category	Bodies & Covers

Features

connection	Tapered Female Threaded
Form	8

Material, Color, and Finish

Color	Gray
Finish	Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat)

Dimensions and Weight

Height	2.78
Hub Size	1-1/2
Length	10.38
Width	4.03

Descriptions

Description	1-1/2" COND BODY
extra long description	APP T58 1-1/2 TYPE T FORM 8 BODY
Long Description	FM8 Grayloy-Iron UNILETS Type T Conduit Outlet Body, Hub Size: 1-1/2 IN, Form: 8, Length: 10.38 IN, Width: 4.03 IN, Height: 2.78 IN, Material: Grayloy-Iron, Finish: Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat), Color: Gray,

Product Type	1-1/2 Type T Form 8 Body
Special Features	Accurately tapped, tapered threads for tight, rigid joints and excellent ground continuity;Allow connections for branch runs;Completely interchangeable with Crouse-Hinds Form 8 bodies, gaskets and covers;Connect and change direction of conduit runs;Equivalent FM8 and Form 8 units have identical applications and installation dimensions;Fits flush and snug against flat surfaces for more stable installation;Flat back design provides greater cubic content for easier wire pulling and more room for splicing;Make



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3942 Automation Way
80525-0000, CO Fort Collins
Phone: 970-305-3593
Fax: 970-372-1731

Manufacturer Information

Brand	Appleton
GTIN	00781381744355
UPC	781381744355

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Type T Conduit Outlet Body

Packaging

Carton	1
Package	5
Weight Per each	5.65

Uses, Certifications, and Standards

Application	For Use With Rigid Steel Conduit And IMC
standard	UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1