



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TM874DBCC6 4W Deco SW 15A 120/277V DRK Brnze *Pass & Seymour/Legrand*

Catalog Number	TM874DBCC6
Manufacturer	Pass & Seymour/Legrand
Description	15A 120/277V Switch Decorator 4-Way, Dark Bronze
Weight per unit	0.2820 (lbs/each)
Product Category	Gen Purpose Switches

### Features

actuator	Rocker switch
amperage rating	15
Contact Rating	120V
Material	Thermoplastic
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Poles	4-Way, Single Pole
Switch Type	Paddle
Voltage	120/277 V
Voltage Rating	120

### Material, Color, and Finish

Color	Dark Bronze
-------	-------------

### Dimensions and Weight

Size	1.27" Depth x 1.43" Width x 4.19" Height
------	--

### Descriptions

Description	4W DECO SW 15A 120/277V DRK BRNZE
extra long description	P&S TM874DBCC6 4W DECO SW 15A 120/2
Long Description	15A 120/277V Switch Decorator 4-Way, Dark Bronze
Product Type	4W Deco SW 15A 120/277V DRK Brnze
Special Features	Everyone wants a home that's a step above ordinary. Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes.

### Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007029468
Manufacturers Part Number	TM874-DBCC6
UPC	785007029468



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Decorator Switch

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Weight Per each	0.282

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximun continuous +115°C, minimum -40°C
standard	CULUS, CSA Listed, UL Listed