

Specifications



Photo is representative



Eaton TMR5Y05120

TMR5 Series Time Delay Relays, Octal style terminals, 8 pins, Repeat cycle (ON time first followed up off time and repeating), 0.1-10 sec time delay, 120 Vac/dc input voltage, 10A max. allowable load, DPDT contact configuration

General specifications

PRODUCT NAME	Eaton timing relay
CATALOG NUMBER	TMR5Y05120
UPC	786685124926
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	2.4 in
PRODUCT WIDTH	1.7 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed (when used with Eaton socket) cRUus
CATALOG NOTES	Fixed time delay settings are available for orders of 50 pieces or more. Contact EatonCare for additional information at 877-ETN-CARE (386-2273). Dual knob unit with independently selectable/adjustable ON/OFF times.



Powering Business Worldwide

Product specifications

TYPE	Timing relay
PROD LOAD	10A
NUMBER OF PINS	8
OPERATING MODE	Repeat cycle (ON time first followed up off time and repeating)
CONTACT CONFIGURATION	DPDT
SERIES	TMR5
DIELECTRIC STRENGTH	2000 V between poles
INPUT VOLTAGE	120 Vac/dc
TERMINALS	Octal
TIME DELAY	0.1-10 seconds

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TMR5Y05120](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Photo is representative



Eaton TMR5Y05120

TMR5 Series Time Delay Relays, Octal style terminals, 8 pins, Repeat cycle (ON time first followed up off time and repeating), 0.1-10 sec time delay, 120 Vac/dc input voltage, 10A max. allowable load, DPDT contact configuration

General specifications

PRODUCT NAME	Eaton timing relay
CATALOG NUMBER	TMR5Y05120
UPC	786685124926
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	2.4 in
PRODUCT WIDTH	1.7 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed (when used with Eaton socket) cRUus
CATALOG NOTES	Fixed time delay settings are available for orders of 50 pieces or more. Contact EatonCare for additional information at 877-ETN-CARE (386-2273). Dual knob unit with independently selectable/adjustable ON/OFF times.



Powering Business Worldwide

Product specifications

TYPE	Timing relay
PROD LOAD	10A
NUMBER OF PINS	8
OPERATING MODE	Repeat cycle (ON time first followed up off time and repeating)
CONTACT CONFIGURATION	DPDT
SERIES	TMR5
DIELECTRIC STRENGTH	2000 V between poles
INPUT VOLTAGE	120 Vac/dc
TERMINALS	Octal
TIME DELAY	0.1-10 seconds

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TMR5Y05120](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

