






# TS10-0016



Catalog Number	TS10-0016	Pole Arrangement	Barrier; Potential; Barrier; Potential; Barrier; Potential; Barrier; Solid Neutral; Current Return; Current; Current Return; Current; Current Return; Current
Marketing Product Description	10 Pole Test Switch Configuration 0016		
UPC	784572132320		
Length (IN)	2.906		
Width (IN)	9.5		
Height (IN)	3.5		
Weight (LB)	2.8		
Brand Name	Milbank		
Type	Instrument Rated Metering Test Switch		
Application	Metering Accessory		
Standard	UL Listed		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	20 Ampere		
Number Of Poles	10		
Frequency Rating	60 Hertz		
Connection	Stud		
Material	Bronze Alloy		
Enclosure	No Enclosure		
Insulation	Non Metallic		
Handle Color Arrangement	Red; Red; Red; Black; Black; Black; Black; Black; Black; Black		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



All dimensions are +/- 1/16".  
Drawing views are not to scale.

Version:

**1**

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.