




PASS & SEYMOUR® Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V

TR26252, TR26352

Style meets safety in Pass & Seymour® Tamper-Resistant Decorator Receptacles!

Corrosion-resistant plated-steel mounting strap, durable nylon faces, and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable performance. Ergonomic decorator-style offers a sleek design, while giving the same performance and ease of installation as standard Pass & Seymour devices. Tamper-resistant feature helps you comply with 2014 NEC® Article 406.12 and get the job done right. Screw-pressure-plate back wiring ensures easy installation and excellent electrical connections. These UL listed receptacles are ideal for residential, multi-dwelling, commercial office, and hospitality applications.



FEATURES & BENEFITS

Dual mechanical shutter system to help prevent insertion of foreign objects.

Impact-resistant nylon face for durability.


Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Backed-out tri-drive steel terminal screws for faster installation.

Auto-ground clip assures positive ground.

.032-inch thick brass triple-wipe power contacts for reliable plug retention.

Corrosion-resistant, plated steel strap.



TR26352GRY

FIELD USES / VERTICAL MARKETS

- Residential
- Hospitality/Lodging
- Retail
- Multiple Dwelling
- Office
- Education



PASS & SEYMOUR®

Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Rating A	V	Color	NEMA Configuration No.
Duplex Receptacles Back & Side Wire				
TR26252I	15A	125V	Ivory	5-15R
TR26252W	15A	125V	White	5-15R
TR26252	15A	125V	Brown	5-15R
TR26252GRY	15A	125V	Gray	5-15R
TR26252BK	15A	125V	Black	5-15R
TR26252RED	15A	125V	Red	5-15R
TR26252LA	15A	125V	Light Almond	5-15R
TR26352I	20A	125V	Ivory	5-20R
TR26352W	20A	125V	White	5-20R
TR26352	20A	125V	Brown	5-20R
TR26352GRY	20A	125V	Gray	5-20R
TR26352BK	20A	125V	Black	5-20R
TR26352RED	20A	125V	Red	5-20R
TR26352LA	20A	125V	Light Almond	5-20R



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

PASS & SEYMOUR®

Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V



TECHNICAL INFORMATION

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498
 CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42
 Conforms to NEMA WD-1 and WD-6

Performance

Electrical


Dielectric Withstand Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

Mechanical

Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only.
Product Identification	Ratings are permanent part of the device

Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact




Materials

Face	Nylon
Back Body	Nylon
Line Contacts	.032 260 Brass
Mounting Strap	.042 Zinc-Plated Steel
Ground Contacts	.040 260 Brass
Pressure Plate	.080 Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Auto-Ground Clip	Steel
Mounting Screws	Tri-Drive Steel

Warranty


1 Year

COMPLEMENTARY DEVICES & ACCESSORIES




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




PLUGTAIL™ DEVICES

- Extra Heavy-Duty SpecGrade
- Extra Heavy Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

ALSO AVAILABLE...

- Hospital Grade Devices
- Ground Continuity Monitoring (GCM)
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- PlugTail™ Devices
- Straight Blade Plugs & Connectors
- Weatherproof Boxes & Covers
- Flexcor® Wire Mesh Grips
- SPD & Isolated Ground Devices



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195
www.legrand.ca




PASS & SEYMOUR® Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V

TR26252, TR26352

Style meets safety in Pass & Seymour® Tamper-Resistant Decorator Receptacles!

Corrosion-resistant plated-steel mounting strap, durable nylon faces, and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable performance. Ergonomic decorator-style offers a sleek design, while giving the same performance and ease of installation as standard Pass & Seymour devices. Tamper-resistant feature helps you comply with 2014 NEC® Article 406.12 and get the job done right. Screw-pressure-plate back wiring ensures easy installation and excellent electrical connections. These UL listed receptacles are ideal for residential, multi-dwelling, commercial office, and hospitality applications.



FEATURES & BENEFITS

Dual mechanical shutter system to help prevent insertion of foreign objects.

Impact-resistant nylon face for durability.


Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Backed-out tri-drive steel terminal screws for faster installation.

Auto-ground clip assures positive ground.

.032-inch thick brass triple-wipe power contacts for reliable plug retention.

Corrosion-resistant, plated steel strap.



TR26352GRY

FIELD USES / VERTICAL MARKETS

- Residential
- Hospitality/Lodging
- Retail
- Multiple Dwelling
- Office
- Education



PASS & SEYMOUR®

Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Rating A	V	Color	NEMA Configuration No.
Duplex Receptacles Back & Side Wire				
TR26252I	15A	125V	Ivory	5-15R
TR26252W	15A	125V	White	5-15R
TR26252	15A	125V	Brown	5-15R
TR26252GRY	15A	125V	Gray	5-15R
TR26252BK	15A	125V	Black	5-15R
TR26252RED	15A	125V	Red	5-15R
TR26252LA	15A	125V	Light Almond	5-15R
TR26352I	20A	125V	Ivory	5-20R
TR26352W	20A	125V	White	5-20R
TR26352	20A	125V	Brown	5-20R
TR26352GRY	20A	125V	Gray	5-20R
TR26352BK	20A	125V	Black	5-20R
TR26352RED	20A	125V	Red	5-20R
TR26352LA	20A	125V	Light Almond	5-20R



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

PASS & SEYMOUR®

Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V



TECHNICAL INFORMATION

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498
 CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42
 Conforms to NEMA WD-1 and WD-6

Performance

Electrical


Dielectric Withstand Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

Mechanical

Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only.
Product Identification	Ratings are permanent part of the device

Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact




Materials

Face	Nylon
Back Body	Nylon
Line Contacts	.032 260 Brass
Mounting Strap	.042 Zinc-Plated Steel
Ground Contacts	.040 260 Brass
Pressure Plate	.080 Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Auto-Ground Clip	Steel
Mounting Screws	Tri-Drive Steel

Warranty


1 Year

COMPLEMENTARY DEVICES & ACCESSORIES




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




PLUGTAIL™ DEVICES

- Extra Heavy-Duty SpecGrade
- Extra Heavy Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

ALSO AVAILABLE...

- Hospital Grade Devices
- PlugTail™ Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195
www.legrand.ca